





SUPER TAC® FLASHLIGHT

FL 1 STANDARD	SUPER TAC
	160 LUMENS
	3h 30min
	346m
	30,000 cd



Case Material: 6000 Series machined aircraft aluminum with anodized finish. Available in Black. Unbreakable polycarbonate lens

Dimensions/ Length: 6.62 in. (16.81 cm); Diameter: Major Diameter: 2.20 in. (5.59 cm); Body Diameter: 0.90 in. (2.29 cm)
Weight: 7.1 oz (200 grams)

Light Source: C4® LED, shock-proof w/ 50,000 hour lifetime

Light Output: 160 lumens; 30,000 candela; 346m beam; runs 3.5 hours
Deep-dish parabolic reflector produces a long range targeting beam with optimum peripheral illumination to aid in navigation
Optimized electronics provide regulated intensity

On/Off: Tail cap push button provides one handed momentary or constant "on".

Battery: Two 3V CR123A lithium batteries (included)

- Features:
- IPX7 Rated design; all openings o-ring sealed to resist moisture
 - Serialized for positive identification
 - LED Solid State circuitry provides regulated light output throughout battery life
 - Removable pocket clip
 - Fits Streamlight 69100 Rail Mount, Fits Streamlight 75910 holster
 - Operates with remote switches
 - IR model available with high power IR 850 nm LED, compatible with night vision equipment

Approvals: Most models meet applicable European Community Directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair,replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY,EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit www.streamlight.com for full warranty information.

Item		UPC	Part #
Super Tac - in box	Black	080926-88700-8	88700
Super Tac - in blister	Black	080926-88701-5	88701
Super Tac Kit - in box - includes vertical grip and low profile mount	Black	080926-88706-0	88706
Super Tac IR- in blister	Black	080926-88703-9	88703
See reverse for additional part numbers			



Item	UPC	Part #
Lithium Batteries 2 Pack	080926-85175-7	85175
Lithium Batteries 12 Pack	080926-85177-1	85177
Lithium Batteries 400 Pack	080926-85179-5	85179
Holster	080926-75910-7	75910
Rail Mount	080926-69100-1	69100
AR15/M16	080926-69902-1	69902
Mag Tube Rail	080926-69903-8	69903
Remote Switch w/ 8" Cord	080926-88185-3	88185
Remote Switch w/ Coil Cord	080926-88186-0	88186
Remote Retaining Clip	080926-88178-5	88178
Vertical Grip w/ Rail	080926-69114-8	69114
Low Profile Mount	080926-88118-1	88118



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. Super Tac 2 / 16