

E-Flood® FireBox® Rechargeable Lantern

FL 1 STANDARD	HIGH	LOW
	615 LUMENS	330 LUMENS
	8h	18h
	126m	93m
	4000 cd	2150 cd



Specific lighting needs require specific tools. With the right lighting tool, you can identify potential or existing problems before they interrupt your ability to get the job done. In addition the costs savings of using the right tool over time will benefit your bottom line.

There is a real need to cut costs wherever possible, yet we cannot afford to forget about environmental issues. Streamlight rechargeable lighting tools make good economic environmental sense. Over time they cost significantly less to operate; and they reduce the amount of batteries used, thereby relieving the problem of battery disposal. With Streamlight rechargeable flashlights, your plant will not only save on the cost of batteries, you'll save the time that's wasted when you discover your light isn't working and the steps involved in getting and replacing batteries.

Case Material: High-impact ABS thermoplastic housing. Rubberized impact bumper, lens ring and cushioned-grip handle.

Dimensions/Weight: Length: 11.5 in. (29.2 cm) Width: 5.1 in. (13 cm) Height: 7 in. (17.8 cm) 7.9 lbs (3.58 kg) with battery (included in purchase)

Light Source: Six (6) C4® LEDs, impervious to shock with a 50,000 hour lifetime and two (2) user programmable ultra bright blue tail-light LEDs. 6 wide pattern parabolic reflectors produce a smooth flood pattern. Optimized electronics provide regulated intensity. Jumper selectable high or low setting.

Battery: Zero-maintenance 6V, 12Ah sealed lead acid battery. Red and green LEDs give charge status feedback.

Models: Standard System - International safety orange or high-visibility yellow; includes shoulder strap; includes AC/DC chargers and mounting rack; ideal for field maintenance, inspection of construction sites, and remote equipment.

Vehicle Mount System - International safety orange or high-visibility yellow; comes with vehicle-mountable hard-wire rack and shoulder strap.

- Features:**
- Toggle switch for easy use with gloves
 - LED Solid State circuitry provides regulated light output throughout battery life.
 - IPX4 Rated for weather resistant operation
 - Serialized for positive identification.
 - Locking charge rack option

Approvals:** Most models meet applicable European Community Directives.
Charge rack meets requirements of NFPA 1901-14.1.11.2 (2003) mounted in any position.

Warranty: Streamlight warrants this product to be free of defect for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work or that you manage to break as long as you own it. Of course, this limited lifetime warranty excludes abuse, batteries and chargers.

Item	UPC	Part #
Standard System - AC/12V DC, shoulder strap & mounting rack		
E-Flood FireBox Standard System 230V - Orange	080926-45812-3	45812
E-Flood FireBox Standard System 230V - Yellow	080926-45828-4	45828
E-Flood FireBox Standard System 240V - Orange	080926-45813-0	45813
E-Flood FireBox Standard System 240V - Yellow	080926-45829-1	45829
E-Flood FireBox Standard System 120V - Orange	080926-45811-6	45811
E-Flood FireBox Standard System 100V - Orange	080926-45814-7	45814
E-Flood FireBox Standard System 100V - Yellow	080926-45830-7	45830
Vehicle Mount System 12V DC, shoulder strap		
E-Flood FireBox Vehicle Mount System - Orange	080926-45815-4	45815
Without Charger		
E-Flood FireBox - Orange	080926-45832-1	45832





Item		UPC	Part #
DC2 direct wire charge cord		080926-22050-8	22050
DC1 Charge Cord		080926-22051-5	22051
120V AC charge cord		080926-22311-0	22311
240V AC charge cord		080926-22241-0	22241
230V AC charge cord		080926-22664-7	22664
100V AC charge cord		080926-22666-1	2266
Locking Device (keyed differently) **Must be factory installed		080926-40163-1	40163
Locking Device (keyed alike) **Must be factory installed		N/A	40164-525
Quick Release Strap		080926-44050-0	44050
Shoulder Strap		080926-45232-9	45232
Standard System Mounting Rack	Orange	080926-45070-7	45070
Direct Wire 12V DC Mounting Rack	Orange	080926-45071-4	45071
Standard System Mounting Rack	Yellow	080926-45072-1	45072
Direct Wire 12V DC Mounting Rack	Yellow	080926-45074-5	45074
Sealed Lead Acid Battery		080926-45937-3	45937
E-Flood Upgrade Kit		080926-45842-0	45842

