






Argo® HAZ-LO® Headlamp

FL 1 STANDARD	LOW	HIGH
	20 LUMENS	90 LUMENS
	50h	8h
	53m	113m
	700cd	3,200cd



Far-reaching beam illuminates objects at a distance



Case Material: Tough ABS thermoplastic construction with elastomer over mold; polycarbonate lens

Dimensions/Weight: Face Cap Diameter: 1.75 in. (4.45cm) Maximum Width: 2.70 in (6.85 cm)
Maximum Depth (including head strap mounting plate): 2.40 in. (6.09 cm)
5.40 oz (153.0 grams) with batteries

Light Source/Output: C4 LED technology, impervious to shock with a 50,000 hour lifetime;
Two lighting modes:
- Low for extended run time and when a less intense beam is ideal: 20 lumens, 700 candela; 53m beam; runs 50 hours
- High for maximum output with a long-range beam distance: 90 lumens, 3, 200 candela; 113m beam; runs 8 hours

On/Off: Push-button sequences through Low, High and Off
Easy to use with gloves; recessed to prevent inadvertent activation

Battery: Three "AAA" alkaline batteries (included)

Features:

- Rubber hard hat strap and elastic strap
- 90 degree tilting head with a durable ratcheting system
- IPX4 water-resistant
- 2 meter impact resistance tested

Approvals: Class 1, Division 1, Groups A,B,C,D; Class II, Division 1, Groups E,F,G; Class III, T-Class: T4 Exia
Most models meet applicable European Community Directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item Description	UPC	Part #
Argo HAZ-LO - Yellow	080926-61026-2	61026

Made in China



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc .Argo HAZ-LO 9/14