

# STYLUS PRO® USB RECHARGEABLE PENLIGHT

FL 1 STANDARD	C4 WHITE LED
	70 LUMENS
	3h 30min
	50 m
	630cd



Case Material/Lens: Anodized aluminum construction. Gasket sealed glass lens

Dimensions/Weight: Length: 6.15 in. (156 mm) Body Diameter: 0.74 in. (19 mm)  
1.9 oz (53.8 grams) with battery

Light Source: White C4® LED, impervious to shock with a 30,000 hour lifetime

On/Off: Push button tail switch – momentary or constant on operation

Battery/Charging: Lithium ion battery rechargeable up to 300 times; fully charges in 2.5 hours  
Charges via USB port or AC wall adapter  
Charge indication LED: LED Red – Charging; LED Green – Charged

Features:

- Removeable pocket clip
- O ring sealed, sliding cover protects the micro USB charging port
- IPX4 water-resistant; 1 meter impact resistance tested

Approvals: Most models meet applicable European Community Directives  
CEC compliant



Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.



Item Description	UPC	Part #
Stylus Pro USB with 120V AC adapter, USB cord, nylon holster. Black with white LED	080926-66133-2	66133
Stylus Pro USB with USB cord, nylon holster. Black with white LED	080926-66134-9	66134
Stylus Pro USB with International AC adapter, USB cord, nylon holster. Black with white LED	080926-66135-6	66135
Stylus Pro USB Battery	080926-66143-1	66143
USB Cord	080926-22057-7	22057
120V AC Wall Adapter	080926-22058-4	22058
International Wall Adapter	080926-66029-8	22059
12V DC USB Adapter	080926-22069-0	22069
EPU-5200	080926-22600-5	22600



30 Eagleview Road • Eagleview, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax  
www.streamlight.com ©Streamlight, Inc Stylus Pro USB 1/16