


STI Motion Detector Cages



PRODUCT OVERVIEW

These super tough cages are extremely effective in reducing malfunctions and high maintenance costs where vandalism or accidental damage is prevalent. They are constructed of heavy-duty steel wire with corrosion resistant polyester coating. Seven sizes are available, two of which are designed to fit motion detectors for corner mount units and the others to fit wall mount applications. All are backed by a three year guarantee against breakage in normal use.

HOW IT WORKS

A simple 4 fixing point installation makes them easy to mount, and removal is simple for servicing the protected device. They are highly recommended for areas where abuse to motion detectors is severe.

KEY FEATURES

General Information

- These super tough cages are extremely effective in reducing malfunctions and high maintenance costs where vandalism or accidental damage is prevalent.
- Three year guarantee against breakage in normal use.

Design

- These steel cages are designed to protect a security PIR/motion detector from vandalism and misuse.
- Designed so there is no interference with the operation of the protected unit.

Construction

- Constructed from plastic coated, heavy-duty galvanised steel rod.

Installation

- A simple 4 fixing point installation can retrofit over existing devices.
- Fast and easy installation.
- Simple removal for servicing of devices.

Options

- Where additional security is required, tamper resistant screws and matching bits are available.



STI Motion Detector Cages

Dimensions and Technical Information

MODELS AVAILABLE

STI-9618*	Motion Detector Damage Stopper - Corner mount
STI-9619*	Motion Detector Damage Stopper - Corner mount
STI-9620	Motion Detector Damage Stopper
STI-9621	Motion Detector Damage Stopper
STI-9622	Motion Detector Damage Stopper
STI-9623	Motion Detector Damage Stopper
STI-9624	Motion Detector Damage Stopper


Accessories:

IP-P035	Tamper resistant screws, #8 x 1 1/2" snake eye (Qty. 4)
TT001/A	Tamper bit for tamper resistant screws

Product Code	Height	Width	Depth
STI-9618*	117mm	136mm	76mm
STI-9619*	196mm	136mm	142mm
STI-9620	156mm	102mm	57mm
STI-9621	171mm	146mm	108mm
STI-9622	222mm	102mm	95mm
STI-9623	196mm	145mm	152mm
STI-9624	225mm	140mm	120mm

* Corner application

**NB Cage sizes may vary from -5 to +5 millimetres



**Safety Technology
International (Europe) Ltd**

UK Office

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU, England

Tel: +44 (0)1527 520 999
Fax: +44 (0)1527 501 999
info@sti-europe.com
www.sti-europe.com

USA Head Office

2306 Airport Road
Waterford, Michigan
48327 - 1209

Tel: +248-673-9898
Fax: +248-673-1246
Toll-free: 0800-888-4STI
info@sti-usa.com
www.sti-usa.com