

3AA HAZ-LO® Division 1 Headlamp

FL 1 STANDARD	3AA HAZ-LO
	120 LUMENS
	11h
	165m
	6800 cd



Case Material: Impact resistant engineering resin case offering exceptional durability and weather resistance. All openings are O-ring sealed.

Dims/ Facecap diameter: 1.88 in. (4.76 cm). Maximum Headlight Width: 2.50 in. (6.35 cm); Maximum Headlight Length: 3.08 in. (7.82 cm)
Weight: 4.5 ounces (128 grams); 7.1 ounces; 202 grams (with batteries)

Lens: Unbreakable polycarbonate lens

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime
120 lumens; 6,800 candela; 165m beam; runs 11 hours

On/Off: Push button switch; On, Off. Easy operation even when wearing heavy gloves.

Battery: Three "AA" alkaline batteries (included)

Features:

- Parabolic reflector produces long range brilliance and smooth uniform beam pattern
- Impact-resistant housing - drop-test verified; 1 meter impact resistance tested
- Rubber hard hat strap and elastic strap
- 90 degree tilting head

Approvals:

- UL, C-UL Classified Class 1, Division 1, Groups A,B,C,D, Class II, Division 1, Groups E,F,G Class III, Temperature Code: T4
- MSHA: Permissible Portable Headlight Assembly; Approval No. 20-A070001-0. Tested for use in Methane-air mixtures only.
- Most models meet applicable European Community Directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction

Item	UPC	Part #
3AA HAZ-LO Headlamp Yellow	080926-61200-6	61200

Engineered in USA
Made in China



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight 3AA HAZ-LO 9/15