

9416-2005 PDU's/Mission Critical PDU's - Power Distribution Unit (PDU)

For more Information
please call

1-800-793-2954

**General Description:**

Belden offers a broad selection of Power Distribution Units to accommodate the power requirements for your equipment. This family of durable and versatile power strips will streamline the power cord organization and minimize cord density in your enclosures. A sampling is offered here in a variety of configurations to accommodate a broad range of requirements. However, Belden can supply many other Power Distribution Units to suit specific customer needs. All power strips have a UL and/or c-UL rating refer to the table here for the rating of each specific unit. All units include a 10-foot power cord.

Image

Image:

**Physical Characteristics (Encl-CM)****Dimensions**

Length/Height:	66.25 inches
Depth:	1.30 inches
Width:	1.85 inches

Electrical Configuration**Electrical Configuration - Table 1:**

# Outlets	Mounting	Amps	Volts	Receptacle Type	Plug Type
20	Vertical	20	125V	5-20R	5-20P

Electrical Configuration - Table 2:

Surge Protection	Circuit Breaker	Switch	Monitoring
No	Yes	Yes	No

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

UL Listing:	UL & c-UL Listed 60950
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	06/01/2006

Notes (Overall)

Notes: Receptacles are duplex style.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9416-2005	0	0.000			PWR STRIP ASSY, 20OUT 20AMP

9416-2005 PDU's/Mission Critical PDU's - Power Distribution Unit (PDU)

Revision Number: 0 Revision Date: 01-13-2010

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.