

E-Spot® LiteBox® Rechargeable Lantern

FL 1 STANDARD	HIGH	LOW
	540 LUMENS	330 LUMENS
	7h	15h
	469m	358m
	55,000 cd	32000cd



Specific lighting needs require specific tools. With the right lighting tool, you can identify potential or existing problems before they interrupt your ability to get the job done. In addition the cost savings of using the right tool will benefit your bottom line.

There is a real need to cut costs wherever possible, yet we cannot afford to forget about environmental issues. Streamlight rechargeable lighting tools make good economic environmental sense. Over time they cost significantly less to operate; and they reduce the amount of batteries used, thereby relieving the problem of battery disposal. With Streamlight rechargeable flashlights, your plant will not only save on the cost of batteries, you'll save the time that's wasted when you discover your light isn't working and the steps involved in getting and replacing batteries.

Case Material: High-impact ABS thermoplastic housing. Rubberized impact bumper, lens ring and cushioned-grip handle.

Dimensions/Weight: Length: 11.5 in. (29.2 cm) Width: 5.1 in. (13 cm) Height: 7 in. (17.8 cm) 7.9 lbs (3.58 kg) with battery (included in purchase)

Light Source: 3 shockproof C4® LEDs with a 50,000 hour lifetime. Jumper selectable high or low settings allow selection of more light output or more runtime.

Battery: Zero-maintenance 6V, 12Ah sealed lead acid battery. Red and green LEDs give charge status feedback.

Models: Standard System - International safety orange or high-visibility yellow; includes shoulder strap; includes AC/DC chargers and mounting rack; ideal for field maintenance, inspection of construction sites, and remote equipment.

Vehicle Mount System - International safety orange or high-visibility yellow; includes vehicle-mountable hard-wire rack and shoulder strap.

Power Failure System - International safety orange or beige; includes AC/DC chargers and "smart" power failure circuitry that automatically illuminates the E-Spot LiteBox when the power is lost

Approvals:** Most models meet applicable European Community Directives.
Charge rack meets requirements of NFPA 1901-14.1.11.2 (2003) mounted in any position.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction

Item Description	UPC	Part #
<i>Standard System Standard System with AC/DC charge cords, shoulder strap & mounting rack</i>		
E-Spot LiteBox Std Sys w/ 120V AC/DC - Orange	080926-45851-2	45851
E-Spot LiteBox Std Sys w/ 230V AC/DC - Orange	080926-45852-9	45852
E-Spot LiteBox Std Sys w/ 240V AC/DC - Orange	080926-45853-6	45853
E-Spot LiteBox Std Sys w/ 100V AC/DC - Orange	080926-45854-3	45854
E-Spot LiteBox Std Sys w/ 120V AC/DC - Yellow	080926-45871-0	45871
E-Spot LiteBox Std Sys w/ 230V AC/DC - Yellow	080926-45872-7	45872
E-Spot LiteBox Std Sys w/ 240V AC/DC - Yellow	080926-45873-4	45873
E-Spot LiteBox Std Sys w/ 100V AC/DC - Yellow	080926-45874-1	45874
<i>Vehicle Mount System with DC charge cord and mounting rack</i>		
E-Spot LiteBox Vehicle Mount System - Orange	080926-45855-0	45855
E-Spot LiteBox Vehicle Mount System - Yellow	080926-45875-8	45875

Item Description	UPC	Part #
<i>Power Failure System with AC/DC charge cords, shoulder strap & mounting rack</i>		
E-Spot LiteBox PF Sys w/ 120V/DC - Orange	080926-45857-4	45857
E-Spot LiteBox PF Sys w/ 230V AC/DC - Orange	080926-45858-1	45858
E-Spot LiteBox PF Sys w/ 240V AC/DC - Orange	080926-45859-8	45859
E-Spot LiteBox PF Sys w/ 100V AC/DC - Orange	080926-45860-4	45860
E-Spot LiteBox PF Sys w/ 120V AC/DC - Beige	080926-45867-3	45867
E-Spot LiteBox PF Sys w/ 230V AC/DC - Beige	080926-45868-0	45868
E-Spot LiteBox PF Sys w/ 240V AC/DC - Beige	080926-45869-7	45869
E-Spot LiteBox PF Sys w/ 100V AC/DC - Beige	080926-45870-3	45870
<i>Without Charger</i>		
E-Spot LiteBox (WITHOUT CHARGER) Orange	080926-45856-7	45856
E-Spot LiteBox (WITHOUT CHARGER) Beige	080926-45866-6	45866
E-Spot LiteBox (WITHOUT CHARGER) Yellow	080926-45876-5	45876





Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
240V AC charge cord	080926-22241-0	22241
230V AC charge cord	080926-22664-7	22664
100V AC charge cord	080926-22666-1	2266
Locking Device (keyed differently) **Must be factory installed	080926-40163-1	40163
Locking Device (keyed alike) **Must be factory installed	N/A	40164-525
Quick Release Strap	080926-44050-0	44050
Shoulder Strap	080926-45232-9	45232
Standard System Mounting Rack Orange	080926-45070-7	45070
Direct Wire 12V DC Mounting Rack Orange	080926-45071-4	45071
Standard System Mounting Rack Yellow	080926-45072-1	45072
Direct Wire 12V DC Mounting Rack Yellow	080926-45074-5	45074
Mounting Rack (LiteBox) Beige	080926-45073-8	45073
Sealed Lead Acid Battery	080926-45937-3	45937
E-Spot Upgrade Kit	080926-45845-1	45845



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com E-Spot LiteBox 8/12