

# Plenum Rated False Ceiling Equipment Storage Series

Model: **GB-AVSTOR3, GB-AVSTOR4, GB-AVSTOR5**

Weight Capacity: 50 lb / 22.7 kg.

## Features

- 1** Plenum rated to intertek ETL listing, conforming to UL Standard 2043
- 2** Locking door panel keeps A/V equipment safe
- 3** Fits in standard 2 x 2 ft. or half of 2 x 2 ft. ceiling tile
  - Multiple knockouts for flexibility when running power or signal cables
  - Includes quick-locking cable system for fast installation
  - Eliminates the need for an A/V rack in the room
  - GB-AVSTOR5 features four internal and two external power receptacles, a 1.5 in. NPT pipe coupler, and one external master power on/off switch

The GB-AVSTOR False Ceiling Equipment Storage series stores A/V and IT components above the false ceiling to provide a clean, organized room environment. The line replaces 1/2 or 1 full ceiling tile, with a perforated lid that looks like a standard HVAC return register when closed. The compact GB-AVSTORs extend the lower room area into the ceiling and are sealed to the plenum space above the ceiling tiles to avoid plenum-related building code issues. The GB-AVSTOR5 also features a 1.5 in. NPT Pipe Coupler.



GB-AVSTOR4 replaces half of a standard 2 x 2 ft. false ceiling tile



GB-AVSTOR5 features 1.5 in. NPT pipe coupler to allow for easy pipe adapter integration



Multiple knockouts for ultimate flexibility

# Plenum Rated False Ceiling Equipment Storage

## GB-AVSTOR3, GB-AVSTOR4, GB-AVSTOR5




### Specifications

Weight	Color	Weight Capacity
GB-AVSTOR3 30.44 lb.  13.8 kg	White	50 lb.  22.7 kg
GB-AVSTOR4 21.26 lb.  9.70 kg	White	50 lb.  22.7 kg
GB-AVSTOR5 35.10 lb.  16.0 kg	White	50 lb.  22.7 kg
Warranty	Width x Height x Depth	
Lifetime	GB-AVSTOR3 23.88 x 23.88 x 5.05 in.   606 x 606 x 128 mm	
Lifetime	GB-AVSTOR4 23.88 x 14 x 5.1 in.   606 x 355.6 x 129 mm	
Lifetime	GB-AVSTOR5 23.88 x 23.88 x 5.1 in.   606 x 606 x 129 mm	


### Packaging

Width x Height x Depth	Contents
GB-AVSTOR3 27.25 x 27.25 x 6.5 in.   692 x 692 x 165 mm	Storage Box (x1), Universal Hardware Pack (x1)
GB-AVSTOR4 28 x 16 x 10 in.   711 x 406 x 254 mm	Storage Box (x1), Universal Hardware Pack (x1)
GB-AVSTOR5 28.5 x 28.5 x 10 in.   724 x 724 x 254 mm	Storage Box (x1), Grid Plate (x1), Universal Hardware Pack (x1)

### Accessories

 False Ceiling Adapter <b>PP-FCTA</b>	 Full Tile False Ceiling Adapter <b>PP-FCMA</b>	 Quick Locking Cable System <b>QLCS</b>
--	---	---

### Architectural Drawing



Specifications subject to change without notice

T: 800.368.9700 Int'l: +001.714.632.7100 | [www.mounts.com](http://www.mounts.com) | 1321 S. State College Blvd., Fullerton, CA 92831 USA



Visit [mounts.com](http://mounts.com) to see the complete line of AV solutions from Premier Mounts, including flat-panel mounts, projector mounts, carts/stands, and a full assortment of accessories.  
© 2014 Premier Mounts. All rights reserved. Rev. 01-14-06

Rev. 02-15-09