



Standard Dome Accessories

Accessories for Indoor/Outdoor Ceiling, Wall, Pole and Corner Mounting Solutions


Ceiling Mount Configuration




Wall Mount Configuration with Pole Mount Adapter



Wall Mount Configuration




Wall Mount Configuration with Corner Mount Adapter



Cap Options:

SO-CAP




Works with
SurroundVideo® Omni and
SurroundVideo® Omni G2

SV-CAP



Works with
SurroundVideo® and
SurroundVideo® G5

MD-CAP



Works with
MegaDome® Series,
SurroundVideo® G5 Mini and
MegaVideo® Compact D4SO

Compatible Cameras:



AV-CRMA

Corner Mount Adapter




Features:

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Works with AV-PMJB, AV-WMJB and AV-JBA	
----------------------	--	--

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	13.04" W (331.25mm) x 4.92" H (125mm)	
	Weight	w/o Camera	0.59lbs (0.27kg)



AV-JBA

Junction Box Adapter




Features:

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 3/4" NPT standard	
	Works with AV-PMJB*, AV-WMJB*, D4S-WMT, HSG2-WMT, and MegaView® 2*	

Mechanical	Casing Material	Aluminum	
		IP66 Outdoor Protection Grade	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	4.7" L (120mm) x 4.7" W (120mm) x 1.89" H (48.1mm)	
	Weight	w/o Camera	1.3lbs (0.63kg)



* Replacement part for these models

AV-EBA

Electrical Box Adapter



Features:


- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 3/4" NPT standard	
----------------------	-----------------------------------	--

Compatible with the following:

Parts	Description
AV-JBA	Junction Box Adapter
D4SO	Indoor/Outdoor 4" IP66, IK-10 Surface Mount Dome
HSG2-WMT	Wall Mount for HSG2 Housing
MB2-JBA	Junction Box Adapter for Bell Mount
MegaBall® Dome Cameras	All-in-One Indoor Cameras with 3.3-10mm Vari-Focal Lens. Not compatible with AV-SPMJB or AV-SWMJB.
MegaDome® Series Cameras	All-in-One Indoor/Outdoor Dome Solution with Remote Focus/Zoom option
MicroDome® -S Model	All-in-One Ultra Low Profile Day/Night Indoor or Indoor/Outdoor Surface Mount Dome Cameras

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	4.7" L (120mm) x 4.7" W (120mm) x 0.15" H (4mm)	
	Weight	w/o Camera	0.3lbs (0.13kg)



Quick Installation:

1. Pass cables through the center hole of the adapter plate.
2. Attach the adapter plate to the electrical box (sold separately) using the appropriate hardware and mounting holes.
3. Attach the compatible part noted above.

AV-PMJB




Pendant Mount Bracket with Junction Box



- Features:**
- Easy Installation and Superior Design
 - Heavy Duty Enclosure Protection for Applications in Harsh Environments
 - Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 1.5" NPT Female	
	Works with SurroundVideo® Series, MegaDome® Series, and D4SO	

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	5.87" H (149.31mm) x 4.69" W (119.20mm)	
	Weight	w/o Camera	2.12lbs (0.96kg)



AV-WMJB




Wall Mount Bracket with Junction Box



- Features:**
- Easy Installation and Superior Design
 - Heavy Duty Enclosure Protection for Applications in Harsh Environments
 - Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 1.5" NPT Female	
	Works with SurroundVideo® Series, MegaDome® Series, and D4SO	

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	7.68" L (195.05mm) x 4.69" W (119.20mm)	
	Weight	w/o Camera	2.49lbs (1.13kg)



AV-PMA


Pole Mount Adapter

**Features:**

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Works with AV-PMJB, AV-WMJB and AV-JBA	
----------------------	--	--

Mechanical	Casing Material	Aluminum
	Color	Ivory (Pantone® Cool Gray 1C)
	Dimensions	5.01" W (127.32mm) x 4.92" H (125mm)
	Weight	w/o Camera 0.32lbs (0.15kg)



MD-FMA


Flush Mount Adapter

**Features:**

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Works with MegaDome® Series	
----------------------	-----------------------------	--

Mechanical	Casing Material	Aluminum
	Color	Ivory (Pantone® Cool Gray 1C)
	Dimensions	Ø 8.54" (217mm) x 2.13" H (54.2mm)
	Weight	w/o Camera 1.5lbs (0.68kg)



MD-CAP


Mounting Cap

**Features:**

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 1.5" NPT standard	
	Works with MegaDome® Series, SurroundVideo® G5 Mini and MegaVideo® Compact D4SO	

Mechanical	Casing Material	Aluminum
	Color	Ivory (Pantone® Cool Gray 1C)
	Dimensions	Ø 6.06" (154.1mm) x 2.57" H (65.3mm)
	Weight	w/o Camera 1.02lbs (0.465kg)



SO-CAP


Mounting Cap

**Features:**

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 1.5" NPT Male	
	Works with SurroundVideo® Omni and SurroundVideo® Omni G2	

Mechanical	Casing Material	Aluminum
	Color	Ivory (Pantone® Cool Gray 1C)
	Dimensions	Ø 7.87" (200mm) x 1.6" H (40.7mm)
	Weight	w/o Camera 0.85lbs (0.39kg)



SO-FMA

Flush Mount Adapter




Features:

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Works with SurroundVideo® Omni and SurroundVideo® Omni G2	
---------------	---	--

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	Ø 9.46" (240.3mm) x 3" H (76.4mm)	
	Weight	w/o Camera	1.15lbs (0.52kg)



SV-FMA

Flush Mount Adapter




Features:

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Works with SurroundVideo®	
---------------	---------------------------	--

Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	Ø 8.54" (217mm) x 2.92" H (74.2mm)	
	Weight	w/o Camera	1.3lbs (0.59kg)



SV-CAP

Mounting Cap



Features:

- Easy Installation and Superior Design
- Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility	Compatible with 1.5" NPT standard	
	Works with SurroundVideo® and SurroundVideo® G5	

Mechanical	Casing Material	Aluminum	
		IP66 Outdoor Protection Grade	
	Color	Ivory (Pantone® Cool Gray 1C)	
	Dimensions	Ø 7.4" (189mm) x 4.33" H (110mm)	
Weight	w/o Camera	1.47lbs (0.69kg)	

