
Arecont Vision®

Leading the Way in Megapixel Video™

Standard Dome Accessories

Accessories for Indoor/Outdoor Ceiling, Wall, Pole and Corner Mounting Solutions



AV-CRMA

Corner Mount Adapter



Compatibility

Features:

- · Easy Installation and Superior Design · Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage

· · · [- · · · · · ·]		,	
Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone®	Cool Gray 1C)
	Dimensions	13.04" W (331.2	25mm) x 4.92" H (125mm)
	Weight	w/o Camera	0.59lbs (0.27kg)
0 0 + + (0 0 + + Ø 1.2" (31.7mm)		(125mm)	5.0" (128mm) 00 10 10 10 10 10 10 10 10 10 10 10 10

Works with AV-PMJB, AV-WMJB and AV-JBA

AV-JBA

Mechanical

Junction Box Adapter




Features:

- Easy Installation and Superior Design · Heavy Duty Enclosure Protection for
- Applications in Harsh Environments • Die-Cast Aluminum is Resistant to Impact and Salt Damage

Compatibility Compatible with 3/4" NPT standard Works with AV-PMJB*, AV-WMJB*, D4S-WMT, HSG2-WMT, and MegaView[®] 2* Casing Material Aluminum

oasing wateriar	Aluminum	
	IP66 Outdoor I	Protection Grade
Color	Ivory (Pantone	® Cool Gray 1C)
Dimensions	4.7" L (120mm)	x 4.7" W (120mm) x 1.89" H (48.1mm)
Weight	w/o Camera	1.3lbs (0.63kg)



AV-EBA

Electrical Box Adapter



Features:

- · Easy Installation and Superior Design · Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage


Compatibility

Compatible with 3/4" NPT standard

Compatible with the following	:
Parts	Description
AV-JBA	Junction Box Adapter
D4SO	Indoor/Outdoor 4" IP66, IK-10 Surface Mount Dome
HSG2-WMT	Wall Mount for HSG2 Housing
MB2-JBA	Junction Box Adapter for Bell Mount
MegaBall® Dome Cameras	All-in-One Indoor Cameras with 3.3-10mm Vari-Focal Lens. Not compatible with AV-SPMJB or AV-SWMJB.
MegaDome® Series Cameras	All-in-One Indoor/Outdoor Dome Solution with Remote Focus/Zoom option
MicroDome [®] -S Model	All-in-One Ultra Low Profile Day/Night Indoor or Indoor/Outdoor Surface Mount Dome Cameras

Mechanical

Casing Material	Aluminum	
Color	Ivory (Pantone®	° Cool Gray 1C)
Dimensions	4.7" L (120mm)	x 4.7" W (120mm) x 0.15" H (4mm)
Weight	w/o Camera	0.3lbs (0.13kg)



Quick Installation:

- 1. Pass cables through the center hole of the adapter plate.
- 2. Attach the adapter plate to the electrical box (sold separately) using the appropriate hardware and mounting holes.
- 3. Attach the compatible part noted above.



* Replacement part for these models

AV-PMJB

Pendant Mount Bracket with Junction Box

Dimensions Weight



Features:


- · Easy Installation and Superior Design Heavy Duty Enclosure Protection for Applications in Harsh Environments
- Die-Cast Aluminum is Resistant to Impact and Salt Damage


5.87" H (149.31mm) x 4.69" W (119.20mm)

w/o Camera 2.12lbs (0.96kg)

Compatibility	Compatible with 1.5" NPT Female		
	Works with SurroundVideo® Series, MegaDome® Series, and D4SO		
Mechanical	Casing Material	Aluminum	
	Color	Ivory (Pantone [®] Cool Gray 1C)	

	F.
	. 5.8" (149.3mm)





AV-WMJB

Wall Mount Bracket with Junction Box




Features:


- · Easy Installation and Superior Design · Heavy Duty Enclosure Protection for
- Applications in Harsh Environments • Die-Cast Aluminum is Resistant to Impact and Salt Damage


Compatibility	Compatible with 1.5	5" NPT Female
	Works with Surrour	dVideo® Series
Mechanical	Casing Material	Aluminum
	Color	Ivory (Pantone
	Dimensions	7.68" L (195.0
	Weight	w/o Camera
		7.01
		7.6" 5.0mm)

Works with SurroundVideo® Series, MegaDome® Series, and D4SO


anical	Casing Material	Aluminum		
	Color	Ivory (Pantone [®] Cool Gray 1C)		
	Dimensions	7.68" L (195.05mm) x 4.69" W (119.20mm)		
	Weight	w/o Camera	2.49lbs (1.13kg)	

















Rev 002.002 © 2016 Arecont Vision[®], All rights reserved. Arecont Vision, the Arecont Vision logo, and MegaBall, MegaDome, MegaVideo, MegaView, MicroDome, and SurroundVideo are registered trademarks of the company. Arecont Vision[®]