

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA

Telephone: 773.869.1234 www.tripplite.com

# 2x2 HDMI Matrix Switch for Video and Audio, 1920x1200 at 60Hz / 1080p (HDMI 2xF/2xF)

MODEL NUMBER: B119-2X2









#### Description

Tripp Lite's B119-2X2 is a 2x2 HDMI Matrix Switch that routes high definition video from any two HDMI sources to any two HDMI displays. It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz. The 2x2 Matrix eliminates the need to disconnect and reconnect HDMI sources. It works with any HDMI source that connects to an HDMI display, and each source is accessible at all times by any display by selecting it with an IR remote, or using the RS232 port to switch the unit. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### **Features**

- Share multiple HDMI sources between multiple monitors ( 2 Input, 2 Output )
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Switch between inputs via pushbuttons, remote control, or RS-232 serial
- . Monitors can be located up to 25 ft. from the switch
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz
- . HDCP and EDID compatible
- Mounting hardware included
- · Plug-and-play; No software or drivers required
- · Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

# Highlights

- Share multiple HDMI sources between multiple monitors
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
   60Hz
- Plug-and-play; No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

# **System Requirements**

 For international use, the B110-INT power supply can be purchased separately; it features plugs for the UK, Europe, and Australia

## Package Includes

- B119-2X2 Local Transmitter Unit
- External Power Supply with NEMA 1-15P Plug(Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- 3.5 mm to DB9 Adapter Cable
- Mounting Hardware
- Remote Control
- · Owner's Manual

# **Specifications**

AC Adapter

Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A





PHYSICAL	
Unit Dimensions (hwd / in.)	1.2 x 9.2 x 3.9
Unit Dimensions (hwd / cm)	3.05 x 23.37 x 9.91
Unit Weight (lbs.)	1.45
Unit Weight (kg)	0.66
Color	Black
COMMUNICATIONS	
Port Control	Push Buttons
CONNECTIONS	
Ports	2
Side A - Connector 1	(2) HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

http://www.tripplite.com/products/product-certification-agencies