



3/4" DRIVE SHALLOW IMPACT SOCKETS, 6 POINT, SAE

Black Industrial Finish

Product Code	Size (Inches)	A OAL (Inches)	B Drive End Diameter (Inches)	C Working End Diameter (Inches)	D Broach Depth (Inches)	E Bolt Clearance Depth (Inches)	F Bolt Clearance Diameter (Inches)	G Nose Length (Inches)	H Uses RET RING® Number	I Use O-Ring / Pin
6-618A	9/16	2	1 5/8	1	1 7/32	1 1/32	1/2	1	6-1XS	6-1A / 6-2B
6-620A	5/8	2	1 5/8	1 3/32	1 7/32	1 1/32	1/2	1	6-1XS	6-1A / 6-2B
6-622A	1 1/16	2	1 5/8	1 5/32	1 7/32	1 1/32	1/2	1	6-1XS	6-1A / 6-2B
6-624A	3/4	2	1 5/8	1 1/4	1 7/32	1 1/32	1 1/16	1	6-1XS	6-1A / 6-2B
6-626A	13/16	2	1 5/8	1 3/8	1 7/32	1 1/32	1 1/16	1	6-1XS	6-1A / 6-2B
6-628A	7/8	2	1 5/8	1 1/2	1 9/32	1 1/32	1 1/16	1	6-1XS	6-1A / 6-2B
6-630A	15/16	2	1 5/8	1 9/16	2 1/32	1 1/32	1 1/16	1	6-1XS	6-1A / 6-2B
6-632A	1	2	1 5/8	1 5/8	1 1/16	1 1/32	1 1/16	-	6-1XS	6-1A / 6-2B
6-634A	1 1/16	2	1 5/8	1 11/16	3/4	1 1/32	1 1/16	1 5/16	6-1XS	6-1A / 6-2B
6-636	1 1/8	2 1/8	1 5/8	1 3/4	3/4	1 5/32	1 1/8	1 7/16	6-1XS	6-1A / 6-2B
6-638	1 3/16	2 1/8	1 5/8	1 7/8	3/4	1 5/32	1 9/16	1 7/16	6-1XS	6-1A / 6-2B
6-640	1 1/4	2 1/8	1 5/8	2	13/16	1 5/32	1 1/4	1 7/16	6-1XS	6-1A / 6-2C
6-642	1 5/16	2 1/8	1 5/8	2 1/32	7/8	1 5/32	1 5/16	1 7/16	6-1XS	6-1A / 6-2C
6-644	1 3/8	2 1/4	1 5/8	2 1/8	7/8	1 5/32	1 3/8	1 9/16	6-1XS	6-1A / 6-2C
6-646	1 7/16	2 1/4	1 5/8	2 3/16	7/8	1 5/32	1 7/16	1 9/16	6-1XS	6-1A / 6-2C
6-648	1 1/2	2 1/4	1 5/8	2 1/4	15/16	1 5/32	1 1/2	1 9/16	6-1XS	6-1A / 6-2C
6-650	1 9/16	2 3/8	1 5/8	2 11/32	15/16	1 1/32	1 9/16	1 11/16	6-1XS	6-1A / 6-2C
6-652	1 5/8	2 3/8	1 5/8	2 13/32	1	1 1/32	1 5/8	1 11/16	6-1XS	6-1A / 6-2C
6-654	1 11/16	2 9/16	1 5/8	2 15/32	1 1/32	1 1/32	1 7/16	1 7/8	6-1XS	6-1A / 6-2C
6-656	1 3/4	2 9/16	1 5/8	2 17/32	1 1/32	1 1/32	1 3/4	1 7/8	6-1XS	6-1A / 6-2C
6-658	1 13/16	2 5/8	1 5/8	2 19/32	1 1/8	1 21/32	1 13/16	1 15/16	6-1XS	6-1A / 6-2C
6-660	1 7/8	2 3/4	1 5/8	2 5/8	1 1/8	1 13/16	1 7/8	2 1/16	6-1XS	6-1A / 6-2C
6-662	1 15/16	2 3/4	1 5/8	2 3/4	1 1/8	1 3/4	1 7/8	2 1/16	6-1XS	6-1A / 6-2C
6-664	2	2 7/8	1 5/8	2 13/16	1 1/8	1 13/16	1 7/8	2 3/16	6-1XS	6-1A / 6-2C
6-666	2 1/16	2 7/8	1 5/8	2 7/8	1 3/16	1 13/16	1 7/8	2 3/16	6-1XS	6-1A / 6-2C
6-670	2 3/16	3 3/16	1 5/8	3 1/16	1 5/16	2 1/16	2 1/2	2 1/2	6-1XS	6-1A / 6-2C
6-672	2 1/4	3 3/16	1 5/8	3 1/8	1 3/8	2 3/32	2 1/2	2 1/2	6-1XS	6-1A / 6-2C
6-676	2 3/8	3 1/2	1 5/8	3 1/4	1 7/16	2 7/16	2 17/32	2 13/16	6-1XS	6-1A / 6-2C

Fed. Spec: ANSI B107.2

WS-6-10HA 10 Piece 3/4" Drive Shallow 6 Point Impact Socket Set on Clip Rail

Contents Include:

Product Code	Size (Inches)	Product Code	Size (Inches)	Product Code	Size (Inches)
6-654	1 1/16	6-660	1 7/8	6-666	2 1/16
6-656	1 3/4	6-662	1 15/16	6-670	2 3/16
6-658	1 13/16	6-664	2	6-672	2 1/4
				6-676	2 3/8

WS-6-14HA 14 Piece 3/4" Drive Shallow 6 Point Impact Socket Set on Clip Rail

Contents Include:

Product Code	Size (Inches)	Product Code	Size (Inches)	Product Code	Size (Inches)
6-624A	3/4	6-632A	1	6-640	1 1/4
6-626A	13/16	6-634A	1 1/16	6-642	1 5/16
6-628A	7/8	6-636	1 1/8	6-644	1 3/8
6-630A	15/16	6-638	1 5/16	6-646	1 7/16

WS-6-18TB 18 Piece 3/4" Drive Shallow 6 Point Impact Socket Set packed in Tool Box

Contents Include:

Product Code	Size (Inches)	Product Code	Size (Inches)	Product Code	Size (Inches)
6-628A	7/8	6-640	1 1/4	6-656	1 3/4
6-630A	15/16	6-642	1 5/16	6-658	1 13/16
6-632A	1"	6-644	1 3/8	6-660	1 7/8
6-634A	1 1/16	6-646	1 7/16	6-664	2"
6-636	1 1/8	6-648	1 1/2	6-107	7" EXT
6-638	1 3/16	6-652	1 5/8	6-140B	U-JOINT
				TB-6119A	TOOL BOX

Features

- SUPERTORQUE® lobular openings for greater turning power without deforming the fastener.
- Designed for maximum engagement on 6 point fasteners.
- Suitable for use with pneumatic and electric impact wrenches.
- Specially heat treated for impact use to provide long life, safety, and durability.



Side hole in socket permits use with Snap-on Industrial Brands Tools@Height drive tools such as ratchets, extensions and u-joints



6-620A



WS-6-14HA



WS-6-18TB

