



## Wiring Duct T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

TY1X2WPI6  
78621097503  
Active

Wiring Duct Wide Slot 1 Inch X 2 Inch Rigid PVC Intrinsic Blue

### Features

Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

### General

Style	Wide Slot
Nominal Width (inches)	1
Nominal Height (inches)	2
Material	Rigid PVC
Color	Intrinsic Blue
Adhesive-Backed	No
Mounting Holes	Yes

### Dimension Information

Length (feet)	6
Width (inches)	1.25
Height (inches)	2.10
A (inches)	1.25
B (inches)	2.10
C (inches)	1.25
D (inches)	2.01
E (inches)	0.30
F (inches)	1.36
G (inches)	0.28
H (inches)	0.10
I (inches)	0.80

### Accessories & Components

Cover	TY1CPI6
-------	---------

### Packaging

T&B Order Multiple	120
T&B Inner Pack	6
Package in Units	120
T&B Sold in UOM	Feet
T&B Weight Per UOM	23.3 lbs. per 100

### Application Support

Product Selector	TD_selector_duct_blue
T&B Sales Drawings	wsd-000180
Technical Information	Available on Website

Specifications	Available on Website
Overview	Available on Website
Wire Fill Calculator	Available on Website

**Notes**

Options	Catalog Number must be completed by adding suffix G for Gray, W for White, B for Black, I for Intrinsic Blue. To order Adhesive-Backed duct, add suffix A. To order duct without mounting holes, add suffix NM to catalog number. Contact Customer Service for pricing and availability.  Standard lengths are 6 feet.
---------	--

**Certifications**

RoHS Compliance	Yes
Webcat CE_recognized	Y

**Certifications****For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)