



Wiring Duct T&B Catalog Number:

UPC Number:
Status:
Description:

TY1X4WPB6A
78621099720
Active

Wiring Duct Wide Slot 1 Inch X 4 Inch Rigid PVC Black Adhesive-Backed Features

Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

General

| | |
|-------------------------|-----------|
| Style | Wide Slot |
| Nominal Width (inches) | 1 |
| Nominal Height (inches) | 4 |
| Material | Rigid PVC |
| Color | Black |
| Adhesive-Backed | Yes |
| Mounting Holes | Yes |

Dimension Information

| | |
|-----------------|------|
| Length (feet) | 6 |
| Width (inches) | 1.25 |
| Height (inches) | 4.37 |
| A (inches) | 1.25 |
| B (inches) | 4.37 |
| C (inches) | 1.25 |
| D (inches) | 4.32 |
| E (inches) | 0.30 |
| F (inches) | 3.63 |
| G (inches) | 0.32 |
| H (inches) | 0.10 |
| I (inches) | 1.00 |

Accessories & Components

| | |
|-------|---------|
| Cover | TY1CPB6 |
|-------|---------|

Packaging

| | |
|--------------------|-----------------|
| T&B Order Multiple | 60 |
| T&B Inner Pack | 6 |
| Package in Units | 60 |
| T&B Sold in UOM | Feet |
| T&B Weight Per UOM | 60 lbs. per 100 |

Application Support

| | |
|-----------------------|----------------------|
| Technical Information | Available on Website |
| Specifications | Available on Website |
| Overview | Available on Website |

Wire Fill Calculator

Available on Website

Notes

Options

Catalog Number must be completed by adding suffix G for Gray, W for White, B for Black, I for Intrinsic Blue. To order Adhesive-Backed duct, add suffix A. To order duct without mounting holes, add suffix NM to catalog number. Contact Customer Service for pricing and availability.

Standard lengths are 6 feet.

Certifications

RoHS Compliance

Yes

Webcat CE_recognized

Y

Certifications**For further technical assistance, please contact us...**

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com