



Wiring Duct T&B Catalog Number:

UPC Number:
Status:
Description:

TY2X4WPI6
78621097522
Active



Wiring Duct Wide Slot 2 Inch X 4 Inch Rigid PVC Intrinsic Blue

Features

Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.



General

Style	Wide Slot
Nominal Width (inches)	2
Nominal Height (inches)	4
Material	Rigid PVC
Color	Intrinsic Blue
Adhesive-Backed	No
Mounting Holes	Yes

Dimension Information

Length (feet)	6
Width (inches)	2.25
Height (inches)	4.46
A (inches)	2.25
B (inches)	4.46
C (inches)	2.25
D (inches)	4.33
E (inches)	0.30
F (inches)	3.63
G (inches)	0.33
H (inches)	0.10
I (inches)	1.00

Accessories & Components

Cover	TY2CPI6
-------	---------

Packaging

T&B Order Multiple	60
T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Feet
T&B Weight Per UOM	66.67 lbs. per 100

Application Support

Product Selector	TD_selector_duct_blue
T&B Sales Drawings	wsd-000180
Technical Information	Available on Website

Specifications	Available on Website
Overview	Available on Website
Wire Fill Calculator	Available on Website

Notes

Options	Catalog Number must be completed by adding suffix G for Gray, W for White, B for Black, I for Intrinsic Blue. To order Adhesive-Backed duct, add suffix A. To order duct without mounting holes, add suffix NM to catalog number. Contact Customer Service for pricing and availability. Standard lengths are 6 feet.
---------	--

Certifications

RoHS Compliance	Yes
Webcat CE_recognized	Y

Certifications**For further technical assistance, please contact us...**

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com