



Fork Terminal Flanged Tongue

T&B Catalog Number:

RA1253

UPC Number:

78621081776

Status:

Active

Description:

Nylon Insulated Fork Terminal with Flanged Tongue, Length .93 Inches, Width .38 Inches, Maximum Insulation .136, Bolt Hole #10, Wire Range #22-#16 AWG, Color Red, Copper, Tin Plated, 1,000 Pack


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Fork terminals allow easy installation because screw needs only to be loosened. A flanged-tongue fork with turned up tips provide fo extra holding protection.



General

| | |
|-----------------|---------------------|
| Insulation Type | Insulated Nylon |
| Terminal Series | RA |
| Material | Copper |
| Finish | Electro -Tin Plated |
| Color | Red |
| Wire Range | 22-16 |
| Stud Size | #10 |

Dimension Information

| | |
|-----------------------------|------|
| Maximum Insulation (inches) | .136 |
| Stock Thickness | .03 |
| A (inches) | .93 |
| B (inches) | .38 |
| C (inches) | .26 |
| M (inches) | .68 |

Specifications

| | |
|---------------------|-----------|
| Temperature Rating | 105°C |
| Voltage Rating | 600V |
| Flammability Rating | UL 94 V-2 |

Tooling

| | |
|-------------------|--|
| Tool Charts | Available on Website |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003, WT145A |
| Recommended Tool | ERG4001 |

Packaging

| | |
|-----------------------|-------------------|
| T&B Order Multiple | 1000 |
| T&B Inner Pack | 1000 |
| Package in Units | 10000 |
| Package Type | Bulk |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 2.5 lbs. per 1000 |
| Alternate Package Qty | RA18-10FS |

Application Support

Overview

Available on Website

Wire Guide Tables

Available on Website

Notes

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com