

# Activate your Potential

Certified for



Culture Plus Series  
SC 40 USB MS BLACK



## SC 40 USB MS BLACK

### Activate your potential

Sennheiser SC 40 USB MS BLACK is a single-sided, wired headset for professionals in enterprises and offices using Skype for Business. With its instant fit, excellent sound and refined styling it helps smooth user transition from traditional systems to Unified Communications to activate the full potential of your new communication culture.

### Sound leadership

With Sennheiser Voice Clarity and a noise-cancelling microphone, the SC 40 USB MS BLACK optimizes speech intelligibility in noisy environments to deliver a more natural conversational experience during calls for both caller and listener. Sound enhancement profiles adjust automatically for optimal communication or multimedia use.

### Quality design

With its contemporary styling, the SC 40 USB MS BLACK looks good from front-desk to Skype call. A lightweight headband with leatherette padding flexes and adjusts for a personalized fit and a bendable boom arm positions the microphone perfectly.

### User focus

With its instant-fit features and choice of acoustic foam ear pad or soft leatherette cover, the SC 40 USB MS BLACK immediately provides users with superior comfort. Features an in-line call control unit for seamless call management and Sennheiser ActiveGard® technology to safeguard users from acoustic shock. A carry pouch for transport or storage protects the headset when not in use.


### Features and Benefits:

- Certified for Skype for Business – with integrated call control and USB connector
- Sennheiser Voice Clarity – wideband sound for a natural listening experience
- Noise-cancelling microphone – filters out ambient noise for optimum speech clarity
- Unique contemporary design – crafted with look and feel in mind
- Instant comfort – flexible headband with leatherette padding adjusts for perfect fit
- 2-in-1 ear pad styles – choose between soft leatherette or light acoustic foam for maximum comfort
- Optimized for communication and multimedia – with automatic sound enhancement profiles

- In-line call control unit – simple and functional for easy call management
- Bendable boom arm – ensures optimal microphone position
- Sennheiser ActiveGard® technology protects users from acoustic shock
- Protective carry pouch – for easy storage or transport
- Switchable Noise at Work limiter – in compliance with EU Noise at Work legislation (Directive 2003/10/EC).

## Product Information

<b>Product name</b>	<b>SC 40 USB MS BLACK</b>			
<b>Art. No.</b>	506498			
<b>EAN No.</b>	40 44155 20692 0			
<b>UPC No.</b>	6 15104 27016 9			
<b>Product description</b>	Monaural UC headset for Skype for Business			
<b>General Data</b>				
<b>Wearing style</b>	Headband, monaural (single-sided)			
<b>Cable length</b>	2.1 m / 6.89 ft			
<b>Connector</b>	USB			
<b>Supported operating systems</b>	Microsoft Windows® and Apple Mac OS			
<b>Color</b>	Black leatherette padding on headband and ear pad cover			
<b>Weight: headset, cable and connector</b>	92 g / 3.25 oz			
<b>Microphone</b>				
<b>Microphone type</b>	Noise-cancelling			
<b>Frequency response - communication/telecommunication</b>	150 – 6,800 Hz (Wideband)			
<b>Speaker</b>				
<b>Speaker type</b>	Neodymium Magnet Speaker			
<b>Frequency response - multimedia</b>	60 – 16,000 Hz			
<b>Sound pressure</b>	Max. 113 dB limited by ActiveGard®			
<b>Call control unit</b>				
<b>Features</b>	– Answer/End a call – Volume up/down – Microphone mute – Redial last outgoing call			
<b>Packaging</b>				
<b>Package type</b>	Poly bag with product label on each item			
<b>Dimension of product packaging (W x H x D)</b>	170 x 240 x 60 mm / 6.69 x 9.45 x 2.36 in			
<b>Package weight (incl. product and packaging)</b>	129 g / 4.55 oz			
<b>Units in distributor master carton</b>	40 pcs			
<b>Master carton weight incl. products</b>	6.67 kg / 14.70 lbs			
<b>Dimension of master carton (W x H x D)</b>	385 x 315 x 470 mm / 15.16 x 12.40 x 18.50 in			
<b>Unit pack/end user</b>	1 pc			
<b>Content of delivery</b>				
<b>Box content</b>	– Headset with foam ear pad and leatherette cover – Carry pouch – Quick guide – Safety guide			
<b>Spare Parts</b>				
<b>Product name</b>	<b>Description</b>	<b>Art. No</b>	<b>EAN No.</b>	<b>UPC No.</b>
<b>CB02</b>	Carry pouch for SC 40/70, 10 pcs	506509	40 44155 20743 9	6 15104 27083 1
<b>HZP 46 Black</b>	Leatherette ear pads, 2 pcs	506512	40 44155 20746 0	6 15104 27088 6
<b>HZP 47 Black</b>	Leatherette ear pads, 26 pcs	506513	40 44155 20747 7	6 15104 27089 3
<b>Warranty</b>	2 years			



## Experience Sennheiser

Perfection is always relative: Users have different expectations from their headsets and speakerphones depending on their needs. For professional users, that need is to communicate as effectively as possible.

With Sennheiser's range of headsets and speakerphones, the combination of Sennheiser sound leadership, quality design and build – and a focus on real life usability – give the best performance possible in offices, call centers and Unified Communications environments.

Please visit us at: [www.sennheiser.com/cco](http://www.sennheiser.com/cco)



Sennheiser is one of the world's leading manufacturers of headphones, microphones, wireless transmission systems and high-quality headsets and speakerphones for both business and entertainment.

Drawing on the electro acoustics expertise of Sennheiser and the leading hearing healthcare specialist William Demant, Sennheiser Communications' wireless and wired headsets for contact centers, offices and Unified Communications professionals are the result of Sennheiser's and William Demant's joint leadership in sound quality, design, wearing comfort and hearing protection.

For further information, please visit:  
[www.sennheiser.com/cco](http://www.sennheiser.com/cco)

**Sennheiser Communications A/S**

Industriparken 27 · DK-2750 Ballerup · Denmark