

FJWMPMPAD

TeraSPEED® MPO (female) to MPO (female), InstaPATCH® 360 Pre-terminated Trunk Cable, 12-Fiber, LSZH

Ordering Details

| Part Number | Jacket Color | Breakout Length | Cable Glands | Pulling Grips, qty | Length |
|--|--------------|-----------------|--------------|--------------------|--------|
| FJWMPMPAD-JBF130 | Yellow | Standard | Included | 0 | 130 ft |
| TeraSPEED® MPO (female) to MPO (female), InstaPATCH® 360 Pre-terminated Trunk Cable, 12-Fiber, LSZH, yellow jacket, standard breakout with gland, 130 ft | | | | | |

Construction Materials

| | |
|------------------------------|---|
| Fiber Type | TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2) |
| Total Fibers, quantity | 12 |
| Fibers per Subunit, quantity | 12 |
| Furcation Color | Yellow |

Dimensions

| | |
|----------------------|--|
| Breakout Length | 33 in |
| Cord Length, maximum | 999 ft 999 m |
| Cord Length, minimum | 10 ft 3 m |
| Ordering Note | For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |

General Specifications

| | |
|--------------------------------|---|
| Brand | InstaPATCH® 360 |
| Color, connector A | Green |
| Color, connector B | Green |
| Construction Type | InstaPATCH® 360 trunk/extension/cross-connect, indoor |
| Interface Feature, connector A | Standard |
| Interface Feature, connector B | Standard |
| Interface, connector A | MPO Female |
| Interface, connector B | MPO Female |
| Ordering Note | Not available in the United States or Canada |

Mechanical Specifications

| | |
|-----------------------------------|----------------------------------|
| Cable Retention Strength, maximum | 4.40 lb @ 90 ° 11.24 lb @ 0 ° |
|-----------------------------------|----------------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|----------------|
| RoHS 2011/65/EU | Compliant |

FJW/MPMPAD

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system



Included Products

N-012-MP-8W-F12 (Product Component—not orderable) — Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber

- CS-8W-MP (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber

860366137 (Product Component—not orderable) — TeraSPEED® MPO Female 12 Fiber Connector, green