

Modular Plugs & Crimpers

Platinum Tools has the solution for your twisted pair cable – from connectors and strain reliefs to crimpers and handy kits!


In today's communications world, whether Datacom, Telecom or Video, twisted pair is the cable of choice. Platinum Tools understands cable and connector compatibility and we offer the proper connectors required for various cable types and applications.

In addition to our wide selection of connectivity products, we also have all the right tools for reliable and fast installations!



- RJ11
- RJ12
- RJ22
- RJ45
- Cat 5e
- Cat 6
- Cat6A 10-Gig
- Shielded
- Non-Shielded
- Boots
- Strain Reliefs

See
Inside



Phone: 800.749.5783

Fax: 800.749.5784

California, USA

www.platinumtools.com

We Make Connections EZ!

Strain Reliefs and Boots

We Make Connections EZ!

RJ45 Boots

- Protect the connector
- Prevent tangled messes
- Eliminate broken release/locking tabs
- Relieve stress on cable
- Help maintain radius bend
- Color code designated
- Cover the external ground on shielded connectors
- Manufactured from ABS material



100 Piece Bags: RJ45 boots are also available in retail bags of 25

Color	Standard Cable OD Ranges				Oversized Cable OD Ranges		
	5.5mm OD * (0.217")	6.0mm OD * (0.236")	6.5mm OD * (0.260")	7.0mm OD * (0.275")	7.5mm OD * (0.295")	8.0mm OD * (0.315")	8.5mm OD * (0.344")
● Black	105062	105073	105083	105093	105101	105104	105107
○ White	105066	105077	105087	105097			
● Red	105060	105071	105081	105091	105102	105105	105108
● Orange	105068	105079	105089	105099			
● Blue	105061	105072	105082	105092	105100	105103	105106
● Gray	105063	105074	105084	105094			
● Green	105064	105075	105085	105095			
● Yellow	105065	105076	105086	105096			
● Purple	105067	105078	105088	105098			

RJ45 Boot sizes:

- 5.5mm / 0.217" *
(typically for Cat5e)
- 6.0mm / 0.236" *
(typically for small Cat6)
- 6.5mm / 0.260" *
(typically for medium Cat6)
- 7.0mm / 0.275" *
(typically for large Cat6)
- 7.5mm / 0.295" *
(typically for Cat6/6E/6A)
- 8.0mm / 0.315" *
(typically for Cat6/6E/6A)
- 8.5mm / 0.344" *
(typically for Cat6/6E/6A)

* Max Cable OD

Strain Reliefs

Compatible with all Standard Modular RJ45 Plugs. Maximum cable OD: 6mm/0.235".



Color Coded	Red	Blue	Grey	Green	Yellow	Black
50 Pieces	100030RC	100030BC	100030GYC	100030GRC	100030YC	100030BKC
500 Pieces	105006	105007	105008	105009	105010	105011

EZ-DataLockTM Strain Reliefs

- Patented 'OD-Flex' technology allows for a wide range of cable OD sizes:
 - Maximum cable OD: 6.8mm/0.268"
 - Minimum cable OD: 5.0mm/0.197"
- Materials: Polycarbonate UL, RoHS, CSA & CE compliant on shielded connectors
- Manufactured from ABS material

For all Standard RJ45 Cat5e/6 Modular Plugs

Bulk/100 piece bags – **NOTE:** Locking pins and keys must be purchased separately.

○ Clear	Snag-Proof Strain Relief – Bulk 100/Bag	105041
● Black	Snag-Proof Strain Relief – Bulk 100/Bag	105042
● Red	Snag-Proof Strain Relief – Bulk 100/Bag	105043
● Yellow	Snag-Proof Strain Relief – Bulk 100/Bag	105044
● Green	Snag-Proof Strain Relief – Bulk 100/Bag	105045
● Blue	Snag-Proof Strain Relief – Bulk 100/Bag	105046
● Gray	Snag-Proof Strain Relief – Bulk 100/Bag	105047
○ White	Snag-Proof Strain Relief – Bulk 100/Bag	105048
	EZ-DataLock Locking Pin – Bulk 50/Bag	105049
	EZ-DataLock Key – Bulk 50/Bag	105050

NOTE: Strain reliefs will not work with external ground tab shielded RJ45 connectors

Locking Pin

Key

