



VOYAGER FOCUS UC

You're not just on the call. You're in it.

Focus on work—not the chaos around you.

Active noise canceling

VOYAGER FOCUS UC

KEY FEATURES



- A** Lightweight comfortable design
- B** Three precision-tuned mics
- C** Mute/OpenMic button
- D** Online indicator light and call answer/end
- E** Intuitive volume and music controls
- F** Magnetic desktop charging stand
- G** ANC on/off switch
- H** USB Bluetooth mini-adapter with mute indicator

INCLUDED ACCESSORIES

- Carrying case for portability and storage of headset, USB adapter and charging cable



GLOBAL CUSTOMER CARE

Backed by Plantronics industry leading global service and support.

+1-800-544-4660 (US and Canada)
+1-831-458-7700 (outside US)

Make it your business to hear and be heard with the Plantronics Voyager Focus UC Stereo Bluetooth headset. Move fluidly between PC and smartphone and between work and entertainment with rich, immersive stereo and active noise canceling designed to keep your focus on work, not on the chaos around you.

INTUITIVE/USER FRIENDLY FEATURES

- Works seamlessly across laptops, Bluetooth-enabled desk phones, mobile phones and tablets
- Smart sensors answer calls by simply putting on the headset, mute by taking the headset off and pause/resume music
- Enhanced voice alerts announce caller ID, mute and connection status, talk time level
- Dynamic Mute Alert feature senses and alerts you when you try to talk when muted
- Smart mic boom: wear on either side and maintain locations of R/L stereo and volume/track buttons

GREAT AUDIO ON BOTH SIDES OF THE CALL

- Precision tuned triple-mics with enhanced DSP for superior background noise canceling
- On-demand active noise cancellation so you can focus on your call or work
- High-quality stereo design provides hi-fi stereo sound and an immersive audio experience
- OpenMic button allows you to hear your surroundings when you need to

COMFORT AND DURABILITY

- Leatherette ear cushions wrapped around pillow-soft memory foam
- Cushioned metal headband provides durability while maintaining a comfortable, secure fit
- Easily take the headset on the go with folding ear cushions and included carrying case

OPTIMIZED FOR UNIFIED COMMUNICATIONS

Connects to	Laptops via USB adapter, Bluetooth-enabled desk phones, mobile phones, tablets, and smart watches
Ideal for	Mobile professionals with extensive PC/Mac and mobile communications in noisy environments; featuring Active Noise Canceling and smart sensor technology
Talk/Listen time	Talk time: Up to 12 hours (10 ANC on) Listening time: Up to 15 hours (12 ANC on)
Roaming range	Up to 98 feet (30 meters) with adaptive power (with Class 1 supported devices)
Headset weight	155 grams
Wireless frequency	Bluetooth® v4.1
Audio performance	Active noise canceling technology, wideband (voice), hi-fi stereo, A2DP, DSP
Hearing protection	SoundGuard DIGITAL: protects against sound levels above 118dBA; Anti-startle (during calls) detects and eliminates any large sudden increase in signal level; Time-Weighted Average prevents average daily noise exposure from exceeding 85dBA
Limited warranty	1 year
Models	B825: UC Standard version built for UC applications and softphones from Avaya, Cisco, Skype and more* B825-M: Certified for Skype for Business and Optimized for Microsoft® Lync®

*Download the latest release of Plantronics Hub to get one-touch call answer/end with these softphones.

For more information about the Voyager Focus UC or other Plantronics products, please visit our website at plantronics.com.

