



CONTROLLED POWER COMPANY

Series 800PI Double Magnetic Conversion Line-Interactive Power Conditioner



Series 700A

3 Phase Power Quality

Voltage Regulation, Isolation, & Power Distribution for Clean, Spike Free, Stable Power

Medical Facilities / Labs / Equipment
Government / Commercial Buildings
Broadcast Communications
Telecommunications
Audio-Visual
Concert Halls & Theaters
Wastewater Treatment Plants
Refineries & Chemical Plants
HVAC Equipment
Machine Tools / CNC Equipment
Co-generation & Power Generation
Manufacturing / Automation / Robotics
UPS Bypass & Power Distribution



American Made Products

1Ø Power Conditioner / 60Hz

Controlled Power Model	Size	Voltage	Sola Model	Size
		120/208/240/480v - 120v	63-23-112-4	120va
5DZAX-500-8PI	250va	120/208/240/480v - 120/208/240v	63-23-125-4	250va
5DZZX-500-8PI	500va		63-23-150-8	500va
5DZZX-750-8PI	750va		63-23-175-8	750va
5DZZX-1K-8PI	1kva		63-23-210-8	1kva
5DZZX-1.5K-8PI	1.5kva		63-23-215-8	1.5kva
5DZZX-2K-8PI	2kva		63-23-220-8	2kva
5DZZX-2.5K-8PI	2.5kva			
5DZZX-3K-8PI	3kva		63-23-230-8	3kva
5DZZX-5K-8PI	5kva		63-23-250-8	5kva
5DMZX-8K-8PI	8kva		63-28-275-8	7.5kva
5DMZX-10K-8PI	10kva	208/240/480v - 120/208/240v	63-28-310-8	10kva
5DMZX-15K-8PI	15kva		63-28-315-8	15kva
5DMZX-20K-8PI	20kva			
5DMZX-25K-8PI	25kva			

3Ø 60 Hz

8BLX-10K-7A	10kva	208v - 208/120Y *		
8BLX-15K-7A	15kva			
8BLX-25K-7A	25kva		63TAA320	20kva
8BLX-30K-7A	30kva		63TAA330	30kva
8BLX-45K-7A	45kva			
8BLX-50K-7A	50kva		63TAA350	50kva
8BLX-75K-7A	75kva	480 - 208/120Y *	63TAA375	75kva
8DLX-10K-7A	10kva			
8DLX-15K-7A	15kva			
8DLX-25K-7A	25kva		63TCA320	20kva
8DLX-30K-7A	30kva		63TCA330	30kva
8DLX-45K-7A	45kva			
8DLX-50K-7A	50kva		63TCA350	50kva
8DLX-75K-7A	75kva		63TCA375	75kva
8DNX-10K-7A	10kva	480 - 480/277Y *		
8DNX-15K-7A	15kva			
8DNX-25K-7A	25kva		63TCC320	20kva
8DNX-30K-7A	30kva		63TCC330	30kva
8DNX-45K-7A	45kva			
8DNX-50K-7A	50kva		63TCC350	50kva
8DNX-75K-7A	75kva	600v - 208/120Y *	63TCC375	75kva
8ELX-10K-7A	10kva			
8ELX-15K-7A	15kva			
8ELX-25K-7A	25kva		63TDA320	20kva
8ELX-30K-7A	30kva		63TDA330	30kva
8ELX-45K-7A	45kva			
8ELX-50K-7A	50kva	208/240/480/600v - 208/120Y, 480/277Y *	63TDA350	50kva
8ELX-75K-7A	75kva		63TDA375	75kva
8**X-100K-7A	100kva			
8**X-125K-7A	125kva			
8**X-150K-7A	150kva			
8**X-225K-7A	225kva			
8**X-300K-7A	300kva	480/600v - 208/120Y, 480/277Y *		
8**X-500K-7A	500kva			

* 50HZ and Delta Output Available Upon Request