



CAT 6A U/UTP

STANDARD COPPER CABLING SYSTEM

About nCompass

nCompass is an innovative product offering of structured cabling solutions.

Understanding your communications challenges allows us to offer you multiple, high-performing fiber optic and copper cabling solutions.

nCompass provides you with support, reliability, flexibility, and energy efficient solutions that exceed industry standards and are backed by an extended warranty.

This nCompass™ copper solution combines Ortronics® or Draka CAT 6A U/UTP cabling and Ortronics 610 Series connectivity, offering reliable channel performance that meets the ANSI/TIA-568-C.2 standard and is supported by a Limited Lifetime Warranty.

Connectivity and cabling products that are a part of nCompass “+” systems may be substituted for the listed components. Visit nCompass-systems.com for the full range of products.

System Benefits

- Ortronics connectivity and cords are designed for reliable channel performance
- Backed by a Limited Lifetime Warranty

CAT 6A U/UTP

STANDARD COPPER CABLING SYSTEM

ORTRONICS

610 Series CAT 6A U/UTP TracJacks for Workstation

Description	Part Number
TracJack® 610 Series CAT 6A T568A/B Individual pack	OR-TJ610*

*Standard color is Fog White. Choose from additional colors below by adding suffix designation.

-00	-36	-42	-43	-44	-45	-68	-88	-99
-----	-----	-----	-----	-----	-----	-----	-----	-----

MCZ610 CAT 6A LSZH UTP Patch Cords

Description	Part Number
Patch cord LSZH 4-Pair Clarity CAT 6A UTP	MCZ610xxM-yy

xx = Length 10 = 1meter, 20 = 2 meter, 30 = 3 meter, 50 = 5 meter, 80 = 8 meter
yy = Patch Cord Color 06 = blue 09 = white

610 Series Patch Panels and Jacks

Description	24-Port	48-Port
Flat Panel 610 Series CAT 6A U/UTP	OR-PHD610U24	OR-PHD610U48
Angled Panel 610 Series CAT 6A U/UTP	OR-PHA610U24	OR-PHA610U48
Flat Panel Kit for Panel Jacks	OR-PHDPJU24	OR-PHDPJU48
Angled Panel Kit for Panel Jacks	OR-PHAPJU24	OR-PHAPJU48
Rear Load 10G/CAT 6A Panel Jacks	OR-PJ6A00*	-

*Standard color is Fog White. Choose from additional colors below by adding suffix designation.

-00	-36	-42	-43	-44	-45
-----	-----	-----	-----	-----	-----

CAT 6A U/UTP Cable

Listing	Part No.	Color	Nom. Diameter (mm)	Approx. Weight (kg/km)	Package
LSZH	OR-100UC6ARH-EU-26	Light Blue	(8.8)	(80)	305 Meter Reel

x = Jacket Color: choose from the colors below.

DRAKA

CAT 6A U/UTP Cable

Listing	Part No.	Color	Nom. Diameter (mm)	Approx. Weight (kg/km)	Package
LSZH	60025517	Light Blue	(8.8)	(80)	305 Meter Reel



OR-TJ610



OR-MCZ61030M-09



OR-PHA610U24



OR-PHAPJU48



100UC6ARH-EU-26

