

Wall, Rack, DIN Rail Mounting Brackets




Wall Mount Brackets are small simple "L-shaped" tabs that allow a single Transition Networks' media converter to be mounted anywhere. The brackets are sold in pairs and are available in several sizes and types to match the different sized media converters and space requirements.

DIN Rail Brackets allow stand-alone media converters to be mounted to a DIN Rail, common in industrial environments, in either a flat mount against the DIN Rail or in a vertical mount in which the converter mounts on its edge.

Mini Wall Mount brackets allow a mini media converter to be securely mounted to a wall or any other flat surface.

Mini Mounting Options

RMBM



DRBM



WMBM



Specifications

Weight	1 lb. [0.45 kg]
Warranty	Lifetime

Standard Mounting Options

WMBL; WMBP; WMBS



WMBV; WMBD



RMBU



Ordering Information

WMBD

5" [127 mm] DIN Rail Mount Bracket
Fits all Stand-Alone Converters; Single or Dual Slot ION Chassis

WMBD-E

4.3" [109 mm] DIN Rail Mount Bracket (Extended) Fits all Stand-Alone Converters with piggyback power supply attached

WMBD-F

3.3" [84 mm] DIN Rail Mount Bracket (flat)
Fits all Stand-Alone Converters
3.25" [82 mm] wide

WMBD-FS

3.1" [79 mm] DIN Rail Mount Bracket (flat, small) Fits Stand-Alone Converters 3" [76 mm] wide

WMBJ-V

2.75" [70 mm] Wall mount bracket kit for Analog Video products including: J/VD-TX-01xx, J/VD-MRX-01xx

WMBL

4" [102 mm] Fits Stand-Alone Converters Point System™ & ION

WMBP

5" [127 mm] Fits Single or Dual Slot ION Chassis

WMBS

3.2" [81 mm] Fits Stand-Alone Converters size 3.9" [99 mm]

WMBV

5" [127 mm] Vertical Mount
Fits all Stand-Alone Converters; Single or Dual Slot Point System™ Chassis

WMBV-E

4.7" [119 mm] Extended Vertical Mount Fits all Stand-Alone Converters with piggyback power supply attached

RMBU

Rack mount bracket for stand-alone converters, used with E-MCR-05 and RMS19-SA4-01

Mini Media Converters

WMBM

3.3" [84 mm] Fits all "Mini" Media Converters

RMBM

Rack mount bracket for mini converters, used with E-mcr-05 and RMS19-SA4-01

DRBM

3.3" [84 mm] DIN Rail Mount Bracket for "Mini" Media Converters
Fits all "Mini" Media Converters