

# MIGHTY MO® CABLE MANAGEMENT SYSTEM

## Mighty Mo 10 Rack Accessories

NOTE: Product dimensions are listed by width, height and depth unless specified otherwise.

OR-MM10VMD712



### Mighty Mo 10 Cable Management Cage with Door

Cage design promotes efficient routing of patch cords between racks. Hinged doors allow easy access during moves, adds, and changes. 16" wide cage creates a 12.25" gap between racks. 12" wide cage creates a 8.25" gap between racks for front-to-back routing of equipment cables and patch cords. Both are supplied with four spools and 12 bend-limiting clips. Black.

PART NO.	DESCRIPTION
OR-MM10VMD712	With door, 12.13" x 13" x 7'
OR-MM10VMD716	With door, 16.38" x 13" x 7'
OR-MM10VMD812	With door, 12.13" x 13" x 8'
OR-MM10VMD816	With door, 16.38" x 13" x 8'

NOTE: All cable managers include hardware necessary to mount the cage on the face of two Mighty Mo 6 or 10 racks.

Patent Numbers 6,946,605, 6,968,647 and 7,026,553

OR-MM10AB71612



### Mighty Mo 10 Airflow Baffles

Mighty Mo 10 airflow baffles mount between racks and direct intake and exhaust air on side flow network equipment from cold aisle to hot aisle. Black.

PART NO.	DESCRIPTION
OR-MM10AB71612	For use with 7' x 16" Mighty Mo 10 rack and 12" wide Mighty Mo 10 cage
OR-MM10AB71616	For use with 7' x 16" Mighty Mo 10 rack and 16" wide Mighty Mo 10 cage
OR-MM10AB73012	For use with 7' Mighty Mo 10 Server Rack and 12" wide Mighty Mo 10 cage when rails are spaced at 30" apart
OR-MM10AB73016	For use with 7' Mighty Mo 10 Server Rack and 16" wide Mighty Mo 10 cage when rails are spaced at 30" apart
OR-MM10AB81612	For use with 8' x 16" Mighty Mo 10 rack and 12" wide Mighty Mo 10 cage
OR-MM10AB81616	For use with 8' x 16" Mighty Mo 10 rack and 16" wide Mighty Mo 10 cage
OR-MM10AB83012	For use with 8' Mighty Mo 10 Server Rack and 12" wide Mighty Mo 10 cage when rails are spaced at 30" apart
OR-MM10AB83016	For use with 8' Mighty Mo 10 Server Rack and 16" wide Mighty Mo 10 cage when rails are spaced at 30" apart

NOTE: Includes all hardware necessary to mount between two Mighty Mo 10 racks. Not intended for use with Mighty Mo 6 racks. Patent pending.

OR-MM10VDA7248



### Mighty Mo 10 Vented Door Assemblies

Door design allows mounting to the front or rear of any Mighty Mo 6 or Mighty Mo 10 rack. The double-hinged door pivots to the right or left and is easily removed. Black.

PART NO.	DESCRIPTION
OR-MM10VDA7248	7' x 24" with 8.38" of clearance behind door for use with VMD-style vertical managers
OR-MM10VDA7244	7' x 24" with 4.38" of clearance behind door for use without vertical managers
OR-MM10VDA8248	8' x 24" with 8.38" of clearance behind door for use with VMD-style vertical managers
OR-MM10VDA8244	8' x 24" with 4.38" of clearance behind door for use without vertical managers

NOTE: Door designed to work with Mighty Mo racks assembled in the 19" configuration.