

# Closet Connector Housing (CCH) Panel, SC Adapters

Duplex, UPC, 6 F, Single-mode (OS2)

CORNING

Corning closet connector housing panels (CCH-CP) are offered in a variety of fiber counts for use with LANscape® solutions hardware products for a “one-size-fits-all” approach. Used with factory-installed or field-installable connectors, these panels provide interconnect or cross-connect capability in a housing at main cross-connections, intermediate cross-connections, telecommunication rooms or work areas. Available with a variety of industry-standard adapter types, the CCH-CP provides an efficient way to securely mate two connectors and offers multimode and single-mode applications.

## Features and Benefits

### Universal design approach

One-size-fits-all LANscape® Solutions housings

### Broadest range of fiber count and adapter types

Solutions for all needs

### Colored icon labeling

Easy connector identification



Part Number: CCH-CP06-59



Part Number: CCH-CP06-59

# Closet Connector Housing (CCH) Panel, SC Adapters

Duplex, UPC, 6 F, Single-mode (OS2)

CORNING

## Specifications

### General Specifications

Application	Enterprise Networks, Data Center LAN/SAN
Product Type	Panels & Modules
Fiber Category	Single-mode (OS2)

### Design - Hardware

Connector Polish	UPC
Fiber Count	6
Number of Adapters per Panel	3

### Design Adapter

Adapter Housing Color	Blue
Adapter Housing Material	Composite
Adapter Type	SC duplex
Insert Material	Ceramic

### Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Ordering Information

Part Number	CCH-CP06-59
Product Description	Closet Connector Housing (CCH) Panel, SC adapters, Duplex, UPC, 6 F, Single-mode (OS2)
EAN Code	4056418194936

## Shipping Information

Units per Delivery	1/1
Package Contents	CCH Adapter Panel with installation guide

# Closet Connector Housing (CCH) Panel, SC Adapters

Duplex, UPC, 6 F, Single-mode (OS2)

The Corning logo is a blue square with the word "CORNING" in white, serif, uppercase letters centered within it.

## *Notes*



**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA**

**800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)**

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.