

Closet Connector Housing (CCH) Panel, SC Adapters

Simplex, UPC, 12 F, Single-mode (OS2)

CORNING

Corning closet connector housing panels (CCH-CP) are offered in a variety of fiber counts for use with LANscape® solutions hardware products for a “one-size-fits-all” approach. Used with factory-installed or field-installable connectors, these panels provide interconnect or cross-connect capability in a housing at main cross-connections, intermediate cross-connections, telecommunication rooms or work areas. Available with a variety of industry-standard adapter types, the CCH-CP provides an efficient way to securely mate two connectors and offers multimode and single-mode applications.

Features and Benefits

Universal design approach

One-size-fits-all LANscape® Solutions housings

Broadest range of fiber count and adapter types

Solutions for all needs

Colored icon labeling

Easy connector identification



Part Number: CCH-CP12-3C



Part Number: CCH-CP12-3C

Closet Connector Housing (CCH) Panel, SC Adapters

Simplex, UPC, 12 F, Single-mode (OS2)

CORNING

Specifications

General Specifications

Application	Enterprise Networks, Data Center LAN/SAN
Product Type	Panels & Modules
Fiber Category	Single-mode (OS2)

Design - Hardware

Connector Polish	UPC
Fiber Count	12
Number of Adapters per Panel	12

Design Adapter

Adapter Housing Color	Blue
Adapter Housing Material	Composite
Adapter Type	SC Simplex
Insert Material	Ceramic

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	-----------------------------------------------------------

Ordering Information

Part Number	CCH-CP12-3C
Product Description	Closet Connector Housing (CCH) Panel, SC adapters, Simplex, UPC, 12 F, Single-mode (OS2)
EAN Code	4042673805892

Shipping Information

Units per Delivery	1/1
Package Contents	CCH Adapter Panel with installation guide

Closet Connector Housing (CCH) Panel, SC Adapters

Simplex, UPC, 12 F, Single-mode (OS2)

The Corning logo is a solid blue square with the word "CORNING" in white, serif, uppercase letters centered within it.

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.