

ENERGY STAR® qualified	Yes
80 PLUS compliant	Yes
<b>Mechanical</b>	
Form factor	Convertible minitower
Chassis dimensions (H x W x D) Minitower or desktop orientation	45.53 x 45.02 x 16.79 cm (17.9 x 17.7 x 6.6 in)
<b>Environmental</b>	
Temperature	
• operating	5 °C to 35 °C (40 °F to 95 °F)
• non-operating	-40 °C to 60 °C (-40 °F to 140 °F)
Humidity	
• operating	8 to 85%
• non-operating	8 to 90%
Maximum altitude (non-pressurized)	
• operating	3,000 m (10,000 feet)
• non-operating	9,100 m (30,000 feet)

**Notes:**

- General technical specifications for the workstation are provided in the HP Z400 QuickSpecs (Worldwide—Version 28—January 1, 2011).
- Configuration specifications are supplied in the Parts Included section.

Hewlett Packard and the HP logo are registered trademarks of Hewlett Packard, all rights reserved. All data and dimensions are referenced from the Hewlett Packard QuickSpecs and are subject to change without notice.

Intel is a registered trademark of Intel; Xeon is a trademark of Intel, all rights reserved.

NVIDIA Quadro is a registered trademark of NVIDIA, all rights reserved.

Energy Star is a registered trademark of U.S. Environmental Protection Agency, all rights reserved.

80 PLUS is a registered trademark of Ecos, all rights reserved.

**Ordering information****MHW-WZ4R0-EEDE Management Workstation**

Highest-performance workstation, German localization included

Order number **MHW-WZ4R0-EEDE**

**MHW-WZ4R0-EEUK Management Workstation**

Highest-performance workstation, British English localization included

Order number **MHW-WZ4R0-EEUK**

**MHW-WZ4R0-EEUS Management Workstation**

Highest-performance workstation, American English localization included

Order number **MHW-WZ4R0-EEUS**

**Accessories****MHW-AWLCK-CZ**

Localization (Keyboard): Czech Republic—Czech  
Order number **MHW-AWLCK-CZ**

**MHW-AWLCK-DE**

Localization (Keyboard): Germany—German  
Order number **MHW-AWLCK-DE**

**MHW-AWLCK-DK**

Localization (Keyboard): Denmark—English  
Order number **MHW-AWLCK-DK**

**MHW-AWLCK-ESP**

Localization (Keyboard): Spain—Spanish  
Order number **MHW-AWLCK-ESP**

**MHW-AWLCK-FR**

Localization (Keyboard): France—French  
Order number **MHW-AWLCK-FR**

**MHW-AWLCK-IT**

Localization (Keyboard): Italy—Italian  
Order number **MHW-AWLCK-IT**

**MHW-AWLCK-NL**

Localization (Keyboard): Netherlands—Dutch  
Order number **MHW-AWLCK-NL**

**MHW-AWLCK-NO**

Localization (Keyboard): Norway—Norwegian  
Order number **MHW-AWLCK-NO**

**MHW-AWLCK-RU**

Localization (Keyboard): Russia—Russian  
Order number **MHW-AWLCK-RU**

**MHW-AWLCK-SE**

Localization (Keyboard): Sweden—Swedish  
Order number **MHW-AWLCK-SE**

**MHW-AWLCK-SUI**

Localization (Keyboard): Switzerland—French/German  
Order number **MHW-AWLCK-SUI**

**MHW-AWLCK-UK**

Localization (Keyboard): United Kingdom—British English  
Order number **MHW-AWLCK-UK**

**MHW-AWLCK-US**

Localization (Keyboard): USA — American English  
Order number **MHW-AWLCK-US**

**MHW-AWSP-PCI**

HP Serial Port Adapter z-Series (not built-in)  
Order number **MHW-AWSP-PCI**