

## AXIS T91L61 Wall-and-Pole Mount

For quick wall and pole installations

Designed for Axis PTZ and multisensor cameras, AXIS T91L61 Wall-and-Pole Mount can quickly connect power and data to the camera through a built-in Ethernet cable with an IP66 RJ45 connector. The ability to choose between an RJ45 or IDC (insulation-displacement contact) connector makes installation flexible. The included mounting bracket can be simply flipped over for flexible mounting on either walls or poles (separate stainless steel straps required for pole installation). AXIS T91L61 is also suitable for corner mounting with an optional accessory. Thanks to its impact-resistant and outdoor-proven material, it can be used in both indoor and outdoor environments.

- > [Flexible installation using the IDC connector](#)
- > [Built-in IP66 RJ45 connector](#)
- > [Suitable for wall and pole mounting](#)
- > [Protection against impact, water, dust and corrosion](#)



## AXIS T91L61 Wall-and-Pole Mount

General	
<b>Supported products</b>	AXIS Q60 Series AXIS Q61 Series AXIS P55 Series AXIS P56 Series AXIS Q37 Series
<b>Casing</b>	Material: Powder-coated aluminum casing Color: White NCS S 1002-B
<b>Sustainability</b>	PVC free
<b>Connectors</b>	Out: IP66 RJ45 Ethernet (male) In: RJ45 Ethernet (female), IDC
<b>Environment</b>	Indoor Outdoor
<b>Operating conditions</b>	-50 °C to 65 °C (-58 °F to 149 °F) Humidity 10–100% RH (condensing)
<b>Storage conditions</b>	-40 °C to 65 °C (-40 °F to 149 °F)
<b>Approvals</b>	<b>Safety</b> IEC/EN/UL 60950-1, IEC/EN/UL 60950-22 <b>Environment</b> IEC 60721, IEC 60721-4 Class 4M3, MIL-STD 810G 509.5, IP66, NEMA 250 Type 4X, RoHS, WEEE
	<b>Impact</b> IEC 62262 IK10
<b>Dimensions</b>	280 x 174 x 152 mm (11 x 7 x 6 in)
<b>Weight</b>	1.85 kg (4 lb)
<b>Maximum load</b>	30 kg (66 lb)
<b>Cable routing</b>	Back: Cable hole Bottom: 3/4" Conduit entrance
<b>Included accessories</b>	Installation Guide
<b>Optional accessories</b>	AXIS ACI Conduit Adapters AXIS T91A64 Corner Bracket Stainless steel straps 700 mm (28 in), 1 pair Stainless steel straps 1450 mm (57 in), 1 pair For more accessories, see <a href="http://www.axis.com">www.axis.com</a>
<b>Warranty</b>	Axis 3-year warranty, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>

Environmental responsibility:  
[www.axis.com/environmental-responsibility](http://www.axis.com/environmental-responsibility)