

# CLARITY® PATCH CORDS

## Clarity UTP Patch Cords

Clarity patch cords utilize center tuned technology to elevate channel performance. Clarity 6A, 6 and 5e cords are ETL verified to Category 6 and 5e component standards. More importantly, center tuning these cords to Clarity jacks and panels provides significant elevation of channel performance that can be field measured.

- Center tuned to Clarity jacks and panels for a more transparent mated union
- Improved Paralign™ 2 plug termination better controls plug performance
- Assembled with premium cordage and 100% factory tested for performance, reliability, and long life
- Narrow Paralign plug profile supports use in high density panels and hubs
- Clarity 6 and Clarity 5E patch cords are ETL verified\* to TIA-568C.2 component specifications to ensure component compliance to project specifications
- Icon compatible—provides additional TIA-606-A designation capabilities

\*NOTE: Low Smoke Zero Halogen Clarity 6 and Clarity 5E modular patch cords are not ETL verified.

OR-MC607-06



### Clarity Modular Patch Cords

Clarity 6 and Clarity 5E PVC modular patch cords are ETL verified to Category 6 and 5e component standards, while providing elevated field-measurable channel performance.

### Low Smoke Zero Halogen Clarity Modular Patch Cords

CLARITY 6 CATEGORY 6 UTP PART NO.	CLARITY 5E CATEGORY 5e UTP PART NO.	DESCRIPTION
OR-MCZ603-06	OR-MCZ5E03-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 3'
OR-MCZ605-06	OR-MCZ5E05-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 5'
OR-MCZ607-06	OR-MCZ5E07-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 7'
OR-MCZ609-06	OR-MCZ5E09-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 9'
OR-MCZ615-06	OR-MCZ5E15-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 15'
OR-MCZ620-06	OR-MCZ5E20-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 20'
OR-MCZ625-06	OR-MCZ5E25-06	Four-pair 24 AWG stranded UTP, blue, LSZH, length 25'

NOTE: To order other standard colors change suffix on MC cords:  
-02 = red, -04 = yellow, -05 = green, -06 = blue, -08 = gray, -09 = white, -00 = black.

### Clarity Modular Patch Cords - PVC

CLARITY 6 CATEGORY 6 UTP PART NO.	CLARITY 5E CATEGORY 5e UTP PART NO.	DESCRIPTION
OR-MC603-06	OR-MC5E03-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 3'
OR-MC605-06	OR-MC5E05-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 5'
OR-MC607-06	OR-MC5E07-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 7'
OR-MC609-06	OR-MC5E09-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 9'
OR-MC615-06	OR-MC5E15-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 15'
OR-MC620-06	OR-MC5E20-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 20'
OR-MC625-06	OR-MC5E25-06	Four-pair 24 AWG stranded UTP, blue, PVC, length 25'

NOTE: To order other standard colors change suffix on MC cords:  
-02 = red, -04 = yellow, -05 = green, -06 = blue, -08 = gray, -09 = white, -00 = black.