

## AXIS F1004 Bullet Sensor Unit

Small bullet-style design for easy installation

AXIS F1004 Bullet Sensor Unit has a highly compact bullet-style design for easy and discreet installation on indoor ceilings and walls. It can rotate and tilt to the desired viewing direction. AXIS F1004 Bullet comprises a fixed lens and an image sensor. It offers a 102° horizontal field of view, a 720p video resolution, and good low-light performance. It has a detachable 8-m (26 ft) cable for connection to an AXIS F Main Unit.

- > **Easy and discreet installation**
- > **Rotates and tilts to the desired viewing direction**
- > **102° horizontal field of view**
- > **HDTV 720p resolution**



## AXIS F1004 Bullet Sensor Unit

Camera		General	
<b>Image sensor</b>	1/4" (effective) progressive scan RGB CMOS	<b>Casing</b>	Plastic
<b>Lens</b>	Fixed iris 2.1 mm, F2.2 Horizontal angle of view: 102° Vertical angle of view: 56°	<b>Operating conditions</b>	-20 °C to 50 °C (-4 °F to 122 °F) Humidity 10–85% RH (non-condensing)
<b>Resolutions</b>	Max 1280x720	<b>Storage conditions</b>	-40 °C to 65 °C (-40 °F to 149 °F)
<b>Wide dynamic range</b>	WDR	<b>Approvals</b>	IEC/EN/UL 60950-1, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78, EN 55024, EN 61000-6-1, EN 61000-6-2, EN 61000-3-2, EN 61000-3-3, EN 50581, IEC 60529 IP3x, EN 55022 Class B, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24
<b>Minimum illumination</b>	Color: 0.4 lux	<b>Dimensions</b>	60 x 60 x 89 mm (2 3/8 x 2 3/8 x 3 1/2 in)
<b>Shutter time</b>	1/24500 s to 1/6 s	<b>Weight</b>	55 g (0.12 lb)
<b>Camera angle adjustment</b>	Pan: ±180° Tilt: 0 to 90° Rotation ±90°	<b>Required hardware</b>	AXIS F Main Unit
<b>Frame rate</b>	Max 25/30 fps (50/60 Hz)	<b>Included accessories</b>	Installation Guide
		<b>Optional accessories</b>	AXIS F7315 Cable White 15 m
		<b>Warranty</b>	Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>

Environmental responsibility:

[www.axis.com/environmental-responsibility](http://www.axis.com/environmental-responsibility)