

E-MCR-05

12-Slot Media Converter Rack



Flexible Design for growing networks simplify your installation of Transition Networks' stand-alone media converters with the Media Converter Rack. This 19" rack-mountable unit supports up to twelve media converters while the unique design allows for multiple connections, consolidated into a single device, making network connections easier and more efficient.

- **Space Saving Design:** This device is powered by a single internal universal power supply; eliminating the need for the multiple power connections often associated with multiple converter installations. The unit saves space in the wiring closet by providing a means for mounting (12) converters in (3) units of rack space while reducing the number of wall outlet power connections required.
- **Convenience:** The media converters are hot-swappable. They can also be removed from the rack, powered externally, and used as stand-alone units in new applications as your network needs change in the future.
- **Cost Effective:** Easily rack mount the single-wide, 12 volt powered, Transition Networks' media converters that you already own, or buy stand-alone units today and rack mount them in the future.
- **Includes:** (12) Universal rack mount media converter brackets.



(Media Converters Sold Separately)

Specifications

Dimensions	Width: 17" [432 mm] Depth: 15" [381 mm] Height: 4.75" [121 mm]
Power Supply	Universal, internal power supply; AC 85 – 264V, 47 – 63 Hz.
Environment	Operating: 0°C to 50°C Humidity: 10% to 90% (non-condensing) Altitude: 0 – 10,000 ft.
Weight	12 lbs. [5.2 kg]
Compliance	UL Listed, cUL Listed (Canada), CISPR/EN55022 Class A, FCC Class A, CE Mark
Warranty	Lifetime

Ordering Information

E-MCR-05
12-Slot Media Converter Rack

Optional Accessories (sold separately)

Mounting Options

RMBU
Universal Rack Mount Bracket
for Stand-Alone Converters

RMBM
Rack Mount Bracket for
Mini Media Converters

RMS19-SA4-01

4-Slot Media Converter Shelf

- **Space Saving Design:** save rack space in low density deployments: 19" rack mount, 1RU high.
- **Flexible:** mix and match up to 4 Transition Networks stand-alone media converters (excluding double-high models).
- **Non-powered Design:** don't pay for power supplies twice. This low cost design allows the use of the power supplies that ship with the media converter.
- **Power Cord Tie-Downs:** eliminates the accidental disconnection of power supplies from the media converters.
- **Converter Mounting Brackets**
- **Securely mounts the converters to the shelf.**
- **Includes universal rack mount media converter brackets.**
- **Optional Faceplate Blanks** are available to cover up unused slots.
- **Rack mount up to 4 stand-alone devices in 1 unpowered shelf.**



(Media Converters Sold Separately)

Specifications

Dimensions	Width: 17" [432 mm] Depth: 6" [152 mm] Height: 1.75" [44 mm]
Weight	3 lbs. [1.35 kg]
Warranty	Lifetime

Ordering Information

RMS19-SA4-01
4-Slot Media Converter Shelf

RMS19-SA4-01-B
4-Slot Media Converter Shelf with 3 Faceplate
Blanks

Optional Accessories (sold separately)

RMS19-B
Faceplate Kit of 3 Blanks to cover up unused
slots

Mounting Options

RMBU
Universal Rack Mount Bracket for Stand-
Alone Converters

RMBM
Rack Mount Bracket for Mini Media Convert-
ers