

AX104934 Faceplates and Panels - FiberExpress Rack Mount Patch Panel 3U



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Patch Panel, Rack Mount, 3U, Black, rear access door

Usage (Overall)

| | |
|------------------------|---|
| Suitable Applications: | FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room |
| Related Parts: | FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits |

Physical Characteristics (Connectivity)

Capacity

| | |
|----------------|--|
| Max. Capacity: | 4 Strips; 48 Fibers (SC, SCD, ST, FC); 96 Fibers (LCD, MT-RJ). Two 8-inch Splice Tray Kit (A0649869), Two 12-inch Splice tray Kit (A0318904) |
|----------------|--|

Access

| | |
|-------------------|----------------------|
| Front Connection: | Flush |
| Termination Area: | Front Sliding Drawer |

Dimensions

Dimensions:

| Height (in.) | Width (in.) | Depth (in.) |
|--------------|-------------|-------------|
| 4.900 | 19.000 | 12.400 |

Materials

Materials:

| Description | Material |
|-------------|----------|
| Panel | Steel |
| Cover | Lexan |

Color

| | |
|--------|-------|
| Color: | Black |
|--------|-------|

Weight

| | |
|---------|---------|
| Weight: | 16 lbs. |
|---------|---------|

Included Parts

| | |
|-----------------|--|
| Included Parts: | 4 Screws (10x32); 5 Tie Wraps; Identification Label; Caution Label |
|-----------------|--|

Packaging

| | |
|------------|---|
| Packaging: | Individually packaged in a cardboard box. |
|------------|---|

Mechanical Characteristics (Connectivity)

| | |
|------------------------------|----------------|
| Storage Temperature Range: | -40°C To +70°C |
| Operating Temperature Range: | -10°C To +60°C |

Applicable Specifications and Agency Compliance (Overall)

Suitability

| | |
|-----------------------|-----|
| Suitability - Indoor: | Yes |
|-----------------------|-----|

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide P0746744 included with the product or visit our web site at <http://www.belden.com> Item number: AX104934

Product Family

Part Numbers:



AX104934 Faceplates and Panels - FiberExpress Rack Mount Patch Panel 3U

| Description | Item Number |
|-------------------------------------|-------------|
| FiberExpress Rack Mount PP 1U Black | AX100041 |
| FiberExpress Rack Mount PP 2U Black | AX100068 |
| FiberExpress Rack Mount PP 3U Black | AX104934 |
| FiberExpress Rack Mount PP 4U Black | AX100116 |

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------|-------|-------------|-------|-------|-----------|
|--------|-------|-------------|-------|-------|-----------|

Revision Number: 0 Revision Date: 08-14-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.