



Model 1008-AP3800-COVER

Right-Angle AP Joist or Wall Bracket with Black Vanity Cover for Cisco 3800 series

Category: Wall and Hard Ceiling - Surface Mount - Right-Angle Brackets



Mount APs in open ceilings with this convenient joist or wall mounting solution. Quickly install AP in preferred horizontal orientation. Includes two beam clamps and a paintable, plastic vanity cover which is virtually transparent to wireless signal. Ideal for restaurants and retail environments with open ceilings. Conduit, raceways, and cable can be terminated in the bracket to for a clean appearance. The access point can be locked in place using the AP manufacturer's locking features.



Features & Benefits

- Conveniently install and conceal AP in open ceiling environment
- Enables wireless access points to be mounted in preferred horizontal orientation
- Painting the AP may void manufacturers warranty, so Oberon includes a paintable, black plastic vanity cover (please see CONFIGURATIONS)
- T-bar bracket accommodates access points from most vendors; includes features for mounting Cisco AIR-BRACKET directly to the right-angle bracket
- Beam mount clamps allow it to be mounted directly to a beam or truss

Technical Specifications

- Design: Right-angle mounting bracket for securing wireless access points on walls, and on ceiling joists and beams in open ceilings. Designed to mount the access point in the preferred horizontal orientation. Includes beam clamps and black vanity cover for AP. Designed for Cisco 3800 series APs.
- Includes adjustable T-bar bracket for attaching most vendors' APs, black beam clamps and hardware
- Construction: 10 ga. black powder-coated steel
- Includes Oberon Model 33-AP3800-COVER, attachable, paintable black UL94-5VA ABS plastic vanity cover, transparent to wireless signal
- Accommodates wireless access points up to 9" x 9"
- Size: 8.5 inches by 7 inches by 3 inches (215 mm by 178 mm by 76 mm)

Standards for Safety

- UL-95-5VA ABS plastic vanity cover

Configurations

Model Number Guide:

Model Number	Includes Vanity Cover #	Designed for AP Model
1008-AP-COVER	33-AP-COVER	Cisco and Aruba APs (except Cisco 3800 series)
1008-MR-COVER	33-MR-COVER	Meraki MR32, MR34, and MR42 APs
1008-AP3800-COVER	33-AP3800-COVER	Cisco 1830, 1850, 2800, 3800 series APs
1008-HLA-COVER	33-HLA-COVER	Cisco HLA AP and Antenna

Measurements *(Maximum values):*

- Height: 8.5 in.
- Width: 7.00 in.
- Depth: 3.00 in.
- Item Weight: 2.5 lbs.
- Shipping Weight: 3 lbs.

Includes

- (1) Right-angle mount
- (2) Beam clamps
- (1) T-bar bracket
- (1) Wire tie
- (1) Vanity cover (please see CONFIGURATIONS)
- (2) Interlocking adhesive strips
- (2) #6 - 32 screw (for attaching T-bar bracket)
- (4) #8 - 32 screw (for attaching access point mounting plate)
- (1) Installation instructions

Available Accessories

- [39-HLA-PLATE](#) - Bracket accessory for Cisco Hyperlocation Antenna
- [39-1008-SPKRMNT](#) - Mounting bracket assembly for the Model 1008/1009 series

Videos - <https://www.youtube.com/user/oberoninc>

1008 Series Installation Video [View at https://youtu.be/pTQ-63wLtdY](https://youtu.be/pTQ-63wLtdY)

Documentation Links

 [Spec Sheet](http://oberoninc.com/index.php?option=com_content&view=article&id=2621&Itemid=399) - oberoninc.com/index.php?option=com_content&view=article&id=2621&Itemid=399

 [Installation Instructions](http://oberoninc.com/images/WebDocs/Model1008-00_Installation_Instructions.pdf) - oberoninc.com/images/WebDocs/Model1008-00_Installation_Instructions.pdf

 [Customer Prints](http://oberoninc.com/images/WebDocs/Model1008-AP3800-COVER_Customer_Print.pdf) - oberoninc.com/images/WebDocs/Model1008-AP3800-COVER_Customer_Print.pdf

 [SECTION 27_21_33 DATA COMMUNICATIONS WIRELESS ACCESS POINTS](#) -

http://oberoninc.com/images/WebDocs/SECTION 27_21_33 DATA COMMUNICATIONS WIRELESS ACCESS POINTS.pdf

 [Model Viewer available at oberoninc.com](#)

Images and documents may depict similar models in the product series.

Dimensional Images

