

NEC Touch Overlay Accessories

Maximum Message. Minimal Expense.



Protective Touch Overlay for NEC Large Screen Displays

Multi-Touch Functionality

Maximize interactivity with multi-touch display support

- IR touch technology enables up to 10 simultaneous touches for interaction and collaboration of content
- Ultra-fast response time allows for split second reactions between touch point and screen

Superior Design

Promote extended use with a high-performance design

Swipe zone around active area allows for full Windows 7, 8, and 10 compatibility

Full steel chassis combined with tempered protective glass ensures the safety of the LCD panel

Easy Integration

Unrivaled simplicity makes installation easier and faster

Maximum compatibility with full HID compliance for numerous Windows, and Mac® operating systems

Fits over existing bezel and attaches utilizing minimal hardware

Future-proof



In order to keep up with the ever-changing world of information technology, the NEC overlay solution contains a revolutionary black swipe zone that borders the active area of the displays and allows for content to be moved in and out with Windows® 8 swipe compatibility.

This area also allows for unrestricted access to the IR sensor, Power LED and ambient light sensor - portions of displays that are often covered up with typical overlay solutions.



Simple 3-Step

The overlay utilizes screw holes that are already located in the display and full installation follows three primary steps:

- 1: Remove screws
- 2: Attach overlay
- 3: Replace screws



Integration of the NEC overlay solution is simple and fast so that less time is spent installing and more time is spent interacting.

Compliant

Built to fit almost any interactive design, the NEC overlay solutions are HID compliant with the following operating systems*:

Windows: Windows XP, Windows Vista, Windows 7, Windows 8

Mac: Up to Mountain Lion OS X

Android: NEC OPS-DRD

*Number or touches dependent on operating system

	OL-V323 -2	OL-V423	OL-V463	OL-V552	OL-V652	OL-E705	OL-V801
Compatible with	V323-2	V423	V463	V552	V652	E705, P703	E805, V801
Simultaneous Touches*	10						
Dimensions (Overlay) W x H x D	32.12 x 19.96 x 1.81"	39.9 x 23.8 x 2.0"	43.4 x 25.8 x 1.9"	50.9 x 29.9 x 1.9"	61.5 x 37 x 2.8"	64.1 x 37.7 x 2.5"	74 x 43.3 x 1.8"
Dimensions (w/ display) W x H x D	32.12 x 19.96 x 3.14"	39.9 x 23.8 x 3.4"	43.4 x 25.8 x 3.4"	50.9 x 29.9 x 3.5"	61.4 x 36.3 x 4.9"	61.1 x 37.7 x 4.4"	74 x 43.3 x 4.4"
Weight (Overlay)	19.3 lbs. / 8.3kg	22.7 lbs. / 10.3 kg	25.1 lbs. / 11.4 kg	31.7 lbs. / 14.4 kg	55.1 lbs. / 25.0 kg	72.3 lbs. / 32.8kg	77.8 lbs. / 35.3 kg
Weight (w/ display)	39.2 lbs. / 17.8kg	59.7 lbs. / 27.1 kg	66.8 lbs. / 30.3 kg	90.2 lbs. / 40.9 kg	169.8 lbs. / 77.0 kg	175.9 lbs. / 79.8kg	213.4 lbs. / 96.8 kg
Response Time	6- 16ms						
Included	Installation Instructions, 3m USB Extension Cable, Installation Screws, IR Overlay						

Windows and Mac are trademarks or registered trademarks of their respective holders. All other brand or product names are trademarks or registered trademarks of their respective holders. Product specifications subject to change.

©2016 NEC Display Solutions of America, Inc. and the NEC logo are registered trademarks of NEC.