


FFZH06KC Faceplates and Panels - FX UHD FRAME



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Ultra HD Frames KeyConnect, Empty Frame, 6 Ports

Usage (Overall)

Suitable Applications:	FiberExpress Ultra Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts:	FiberExpress Ultra Patch panels, Pre-terminated MPO low loss cable assemblies

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	6 KEYCONNECT PORTS
----------------	--------------------

Access

Front Connection:	1 inch Pullout
-------------------	----------------

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
1.500	4.500	1.870

Materials

Materials:

Description	Material	Color
FXU HD Frame	Plastic - UL94V-0	Black

Color

Color:	Black
--------	-------

Weight

Weight:	0.035 lbs.
---------	------------

Packaging

Packaging:	Individually packaged in a plastic bag, shipped in cardboard box (50/box)
------------	---

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Storage Temperature Range:	-10°C To +75°C
Operating Temperature Range:	-10°C To +60°C

FFZH06KC Faceplates and Panels - FX UHD FRAME

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	EUP 50

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product, please contact our Technical Support group (ibdn.ts@belden.com) or your local sales representative. Note: This frame can hold KeyConnect Fiber modules and/or KeyConnect UTP copper modules.

Product Family

Part Numbers:

KeyConnect Products	Compatibility
KeyConnect LC Duplex adapter	YES
KeyConnect SC Simplex adapter	YES
KeyConnect ST adapter	YES
KeyConnect 10GX, Cat6+, Cat5e Modular jack	YES
KeyConnect 10GX, Cat6+ Modular coupler	YES (one way)
KeyConnect 10GX, Cat6+, Cat5e Shielded Modular jack	NO
KeyConnect 10GX Shielded Modular coupler	NO
KeyConnect BNC Coax module	YES
KeyConnect Video F Coax (Flush) module	NO
KeyConnect Video F Coax (Recessed) module	YES

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
FFZH06KC	1 EA	0.093 LB			FX UHD KCONNECT FRAME 6 PORTS

Revision Number: 0 Revision Date: 01-07-2016

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.