

SPCN110

SPC PSTN Module

VANDERBILT



SPC PSTN Module

Vanderbilt's SPCN110 offers the ability to expand the SPC system with reporting and SMS functionality.

Key Features include:

- communication
The communication module enables the control panel to communicate with PSTN networks. The SPCN110 primary or secondary communication path for multi-event alarm transmission to SIA/Contact ID standard receivers.
- SMS Reporting
The SPC system can support up to 100 SMS numbers (SPC6xxx) each number can have a unique filter of which events are to be sent.
- Easy mounting and configuration
The modem plugs directly onto the SPC controller main board removing the need for any additional wiring. All the module functions are configurable via the control panel.

Operations:

- SIA
- CID
- SMS events
- Dial up Internet





■ Technical Data

Functional

Network connections	PSTN (analogue telephone network)
---------------------	-----------------------------------

Power and Mechanical

Operating current	Max.35 mA at 12 V DC (communication active)
-------------------	---

Quiescent current	Max. 25 mA at 12 V DC
-------------------	-----------------------

Mounting	Plug on module to SPC controller
----------	----------------------------------

Operating temperature	-10° ~ +50 °C
-----------------------	---------------

Dimensions	90 x 38 x 25 (PCB)
------------	--------------------

Weight	0.030 kg
--------	----------

■ Ordering Data

Type	Art. No.	Description	Weight*
Modem	V54550-B101-A100	SPCN110.000 PSTN module	0.030Kg

* Total weight of the product inclusive of the weight of its accessories and packaging.

■ Additional Ordering Data

Type	Art. No.	Description
SPC Panels		
SPC6350.320-L1	V54541-C118-A100	SPC control panel, 16-512 zones, Ethernet, G5 metal housing
SPC6330.320-L1	V54541-C105-C100	SPC control panel, 8-512 zones, Ethernet, G3 metal housing
SPC5350.320-L1	V54541-C117-A100	SPC control panel, 16-128 zones, Ethernet, G5 metal housing
SPC5330.320-L1	V54541-C107-B100	SPC control panel, 8-128 zones, Ethernet, G3 metal housing
SPC5320.320-L1	V54541-C106-B100	SPC control panel, 8-128 zones, Ethernet, G2 metal housing
SPC4320.320-L1	V54541-C109-B100	SPC control panel, 8-32 zones, Ethernet, G2 metal housing
SPC4320.220-L1	V54541-C114-A100	SPC control panel, 8-32 zones, Ethernet, G2 housing with metal base and plastic cover
Keypads		
SPCK520.100-N	V54543-F115-A100	Compact Keypad with graphical display and audio
SPCK521.100-N	V54543-F116-A100	Compact Keypad with graphical display, card reader and audio
SPCK620.100	V54543-F110-A100	LCD keypad with graphical display
SPCK623.100	V54543-F111-A100	LCD keypad with graphical display, card reader and audio
SPCK420.100	V54543-F101-A100	LCD keypad with 2 x 16 characters
SPCK421.100	V54543-F102-A100	LCD keypad with 2 x 16 characters and integrated card reader
Expanders		
SPCE452.100	V54542-F107-A100	Expander with 8 outputs, back tamper
SPCE652.100	V54542-F106-A100	Expander with 8 inputs and 2 outputs, back tamper
SPCA210.100	V54547-A101-A100	2-door expander
SPCP432.300	V54545-C103-A100	Smart PSU with 2-door expander, G2-housing
SPCP433.300	V54545-C104-A100	Smart PSU with 2-door expander, G3-housing
SPCE110.100	V54542-F104-A100	Keyswitch expander with 2 LEDs and 3-position key switch
SPCE120.100	V54542-F105-A100	Indication expander with 16 LEDs, 4 function keys and integrated card reader
SPCW130.100	V54554-F101-B100	SiWay RF-expander
SPCP332.300	V54545-C102-A100	Smart PSU with 8 inputs and 2 outputs, G2-housing
SPCP333.300	S54545-C101-A100	Smart PSU with 8 inputs and 2 outputs, G3-housing
SPCP355.300	S54545-C105-A100	Smart PSU with 8 inputs and 6 outputs, G5 metal housing
Detectors		
PDM-I12	V54530-F114-A100	MAGIC PIR detector, 12m wide angle
PDM-I18	V54530-F106-A100	MAGIC PIR detector, 18 m wide angle
MK-1400	V54536-F101-A100	Magnetic contact

Accessories

IPAW8-10	V54538-F107-A100	Wireless personal alarm
IRCW6-11	V54543-F109-A100	SiWay remote control, white replaceable battery
IPAW6-10	V54538-F108-A100	Wireless Personal Alarm Button

Verification

SPCV340.000	V54542-F108-B100	Audio expander with 4 inputs and 1 output
SPCV341.000	V54542-F109-B100	Audio expander with 4 inputs and 1 line output
SPCV310.000	V54542-F120-A100	Audio satellite
SPCV440.000	V54542-F118-A100	Combi audio expander for MAGIC motion detectors with 4 inputs and 1 output
SPCV410.000	V54542-F119-A100	Combi audio satellite for MAGIC motion detectors
CCMS2010-IR	S54561-C112-A100	1/2.7" 2MP Compact IP Camera PoE(LAN)

Access

AR6181-MX	6FL7170-8BK	Multi-technology card reader
PP500-EM	V54501-F1-A1	Heavy-duty card and PIN reader
AR6182-RX	6FL7170-8AE	Multi-technology card and PIN reader



Learn more at www.vanderbiltindustries.com