

Protective Covers and Plaster Rings

ADJUSTABLE RINGS

Useful in installation where wall thicknesses are unknown at the time of order or electrical rough in.

Construction: Galvanized steel

ADJUSTABLE RINGS			
	BOX SIZE/DEVICE TYPE	FASTENERS INCLUDED	PG
APR-1-5/8	Single Gang	5/8" to 1 1/4"	FP211051
APR-1	Single Gang	3/4" to 1 1/2"	FP211050
APR-2	Two Gang	3/4" to 1 1/2"	FP211052
APR-3	Three Gang	3/4" to 1 1/2"	FP211053
APR-R	3-0 Round	3/4" to 1 1/2"	FP211054



APR-1



APR-2



APR-3



APR-R

PLASTIC DEVICE COVERS


Attach to the front of receptacles, switches or can be snapped onto empty mud rings to keep them clean, dust free and finish ready during the taping and painting process. The covers are replaced later with faceplates at the trim out phase of construction.



DCP-1T



DCP-2



DCP-3R

PLASTIC DEVICE COVERS			
	BOX SIZE/DEVICE TYPE	FASTENERS INCLUDED	PL
DCP-1	Single Gang Receptacle	(2) #8-32 SCREWS	FP003414
DCP-2	Double Gang Receptacle	(2) #8-32 SCREWS	FP003416
DCP-3	Three Gang Receptacle	(2) #8-32 SCREWS	FP003418
DCP-4	Four Gang Receptacle	(2) #8-32 SCREWS	FP003420
DCP-1T	Single Gang Toggle Switch	(2) #8-32 SCREWS	FP003415
DCP-2T	Double Gang Toggle Switch	(2) #8-32 SCREWS	FP003417
DCP-3T	Three Gang Toggle Switch	(2) #8-32 SCREWS	FP003419
DCP-4T	Four Gang Toggle Switch	(2) #8-32 SCREWS	FP003421
DCP-DT	Dbl. Gang Toggle Switch & Device	(2) #8-32 SCREWS	FP003422
DCP-1R	Single Gang Plaster Ring Only	NONE	FP231068
DCP-2R	Double Gang Plaster Ring Only	NONE	FP231071
DCP-3R	Three Gang Plaster Ring Only	NONE	FP231074
DCP-4R	Four Gang Plaster Ring Only	NONE	FP231077
DCP-R	3" Round Plaster Ring Only	NONE	FP231080

LOW VOLTAGE MOUNTING PLATES

Eliminates the need for an electrical box for Class 2 low-voltage wiring.

Construction: Galvanized steel

LOW VOLTAGE MOUNTING PLATES			
	PKG. QTY.	BOX SIZE/DEVICE TYPE	PG
CBXR	50	Single Gang	F002024
CBX1	100	Single Gang, w/ Screws	F002011



CBXR



CBX1