


UNIVERSAL AP AND ANTENNA ARTICULATING MOUNT



The AccelTex Solutions Universal AP and Antenna Articulating Mount allows an AP and an antenna to be mounted in the same location. The mount can be fastened to a ceiling or wall, to an I-beam or to a piece of all thread. The mount allows both horizontal and vertical articulation of the antenna. This mount includes additional lengthening arms to allow for more antenna articulation and are removable for a more compact solution. This mount is compatible with all AccelTex Antennas. Additional antenna mounting plates are available for other vendor antennas.

Part Number: ATS-APANTARTMNT-UNIV1

> FEATURES

- Universal Design - Includes keyholes for mounting a Cisco AP and an integrated T-bar for mounting other manufacturer APs
- Maximum horizontal and vertical antenna articulation
- Compatible with all AccelTex patch antennas
- Additional adapter plates may be purchased for other manufacturer antennas
- Includes clear degree markings for precise angling of the antenna
- Powder coated finish for indoor or outdoor installation
- Integrated slots for cable management keeps install neat and compact
- Lengthening arms can be used to acquire maximum articulation or can be removed for a more compact installation

> BENEFITS

- Easy to Install
- Versatile compact design compatible with almost every manufacturers AP
- Variety of mounting options including beam clamps, 3/8" All-Thread, flush wall or ceiling mount, or even strap the mount to a pole or custom beam
- Simple, one person installation
- Future proof - Install a new AP or antenna instantly

> MOUNT SHIPS WITH

- QTY (2) Beam Clamps
- QTY (2) Lengthening Arms




AP Mounting Plate




Degree Markings

Positive Stop Articulation



Shown with Beam Clamps and Extension Arms Installed




Shown Wall Mounted with Extension Arms Installed



Shown Wall Mounted with Extension Arms Removed



UNIVERSAL AP AND ANTENNA ARTICULATING MOUNT



The AccelTex Solutions Universal AP and Antenna Articulating Mount allows an AP and an antenna to be mounted in the same location. The mount can be fastened to a ceiling or wall, to an I-beam or to a piece of all thread. The mount allows both horizontal and vertical articulation of the antenna. This mount includes additional lengthening arms to allow for more antenna articulation and are removable for a more compact solution. This mount is compatible with all AccelTex Antennas. Additional antenna mounting plates are available for other vendor antennas.

Part Number: ATS-APANTARTMNT-UNIV1

> MECHANICAL SPECIFICATIONS

Dimensions: 10.7" L x 9.3" W x 11.0" H (271mm L x 237mm W x 281mm H)

Weight: 5.05 lb (2.29 kg)

Color: White

Installation: Wall, Ceiling, I-Beam, 3/8" All-Thread Mount, Metal Strapping

Max Vertical Articulation $\pm 80^\circ$

Max Horizontal Articulation: $\pm 80^\circ$

> ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor or Outdoor

> WARRANTY

1 Year Limited Warranty

> COMPATIBILITY

For use with AccelTex Solutions patch antennas. Additional antenna mounting plates are available for other vendor antennas.

> INCLUDED HARDWARE

Includes beam clamp hardware. Installer is required to provide any additional mounting/fastening hardware for other possible mounting situations.