



Model 9116LP

More flexibility and options in a value priced Business Phone

The 9116LP from Aastra is a fully featured Enterprise-grade telephone offering a wide array of the most sought after features in a rugged day-to-day office telephone. Based on our popular 9116 model, the 9116LP incorporates PBX line power, improved user interfaces and a number of other feature enhancements that can add value and flexibility to any office environment at a price that may surprise you.

With a three line adjustable display, the 9116LP is fully compatible with Call Display and Visual Call Waiting offering

prompts in English, French and Spanish. Additional information is provided by the LED indicator which flashes for message waiting, new call indication, incoming call, extension in use, feature activation and hold. Call management features include an 80 name/number callers list and 20 name/number directory. With speakerphone and 15 autodial positions, the 9116LP offers flawless performance in any environment.

Part of our Value family of analog telephones, the 9116LP is ideally suited for almost any business application from small/home offices to large Enterprise environments.

Key Features and Benefits:

✦ Flexible Deployment Capability

The 9116LP can be deployed in a wide variety of business environments. Whether using standard PSTN service, Centrex or PBX, the 9116LP reliably delivers flawless performance. With a choice of powering via the PBX line or with the included DC power supply, it can be used in most business settings and will support all common CLASS and Voltage Message Waiting indication protocols. And, with a fail to POTS feature, the 9116LP will continue to provide basic telephone service in the event of a power failure.

✦ More Caller Information

The three line adjustable display with contrast control supports Caller ID and Call Waiting Display to provide more information on incoming callers. The bright, well-positioned LED is also used to provide a variety of information from message waiting indication to extension in use. These features enhance productivity by quickly providing "at a glance" information to the user.

✦ Enhanced Call Management

The 9116LP offers storage capacity for Callers List, Personal Directory and Last Number Redial as well as 15 "one touch" autodial positions employing 8 memory keys to facilitate easy of use. On hook dialing using the built-in speakerphone provides additional calling options and the speakerphone can be disabled for office designs not suitable for speakerphones. Predefined hard keys for functions such as Dial, Redial, Hold, Flash and Goodbye allow for efficient call handling in any environment.

Feature Highlights

- ✦ Call Display with Visual Call Waiting
- ✦ PBX Line or DC Powered
- ✦ Speakerphone with Mute
- ✦ 8 programmable memory keys
- ✦ Three line adjustable display with Contrast control
- ✦ Callers List
- ✦ 20-name and number scroll style Directory
- ✦ On-hook dialing
- ✦ Compatible with Centrex, PBX or standard telephone service
- ✦ CLASS/Voltage Message Waiting indicator
- ✦ Programmable Feature On and Off keys with indication
- ✦ Improved User Interface
- ✦ PBX Line Powered
- ✦ Speakerphone with mute and disable capability
- ✦ On and Off Call Waiting ID
- ✦ Pre-Dialing
- ✦ Programmable Feature On and Off keys with indication
- ✦ Visual Message Waiting for 90 volt

Model 9116LP Technical Specifications

Physical

- ✦ 19.1cm W x 19.1cm D x 8.9cm H
- ✦ 1.1 kg
- ✦ Color: Charcoal
- ✦ Wall Mountable
- ✦ Footstand included

Power

- ✦ PBX Line – on hook PBX basic requirements – Minimum Voltage: 22VDC, Maximum Current: 4mA
- ✦ DC wall adaptor included

Audio

- ✦ Hearing aid compatible (HAC) handset
- ✦ Speakerphone with mute and disable capability

Display and Indicator

- ✦ 3 line adjustable LCD display Contrast control. Displays incoming name/number, call waiting, call timer and clock
- ✦ CLASS and Voltage Message Waiting LED indicator. Switchable to support Visual Message Waiting for 110 volt and 90 volt

Feature Keys

- ✦ 4 navigational keys
- ✦ 8 programmable keys, supporting up to 15 autodial positions
- ✦ 13 predefined hard keys:
 - Hold
 - Goodbye
 - Options
 - Callers
 - Dial – supports Predial feature
 - Redial
 - Save
 - Flash
 - Directory
 - Speakerphone/Mute
 - Delete
 - Shift
 - Volume control

Localization

- ✦ Multi-lingual display prompts – English, French, Spanish

Package Contents

- ✦ Doc Kit
 - English and French User guides
 - English and French Directory/Memory Card
 - Directory/Memory Card LENS
 - Number Card LENS
- ✦ Feature Key Plate French
- ✦ Handset and coil cord

- ✦ Footstand
- ✦ DC wall adapter
- ✦ Line Cord, 4 Pos 2 Cond, Charcoal
- ✦ Line Cord 7 inch Charcoal

Part Numbers

- ✦ A1265-0000-10-05 - 9116LP Generic Char E/F
- ✦ D0023-0018-00-00 – 9V DC Power Adapter

EMC

- ✦ FCC Part 15 (CFR 47) Class B
- ✦ ICES-003 Class B

Safety

- ✦ CSA-C22.2 No. 60950
- ✦ UI 60950

Telecom

- ✦ FCC Part 68 (Hearing Aid Compatibility)

Aastra Technologies

155 Snow Blvd.
Concord, Ont., L4K 4N9 - Canada
T 1 905 760 4200
F 1 905 760 4233
www.aastra.com