

Rack PDU 2G, Switched, Zero U, 20 A/208 V, 16 A/230 V, (7) C13 and (1) C19	AP8958
Rack PDU 2G, Switched, Zero U, 20 A/208 V, 16 A/230 V, (21) C13 and (3) C19	AP8959
Backplates and Panels	
Symmetra RM 230 V Backplate kit with (2) IEC 320 C19 and (1) IEC 60309	SYPD10
Symmetra PDU Airflow Management Blanking Panel	SYPD2
Symmetra RM 220-240 V Backplate Kit with (8) IEC 320 C13 and (2) IEC 320 C19	SYPD4
Symmetra RM 2-6 kVA 230 V Hardwire Kit	SYPD9
SY RM PDU 4XC19	SYPD8
Rack-mount Transfer Switches	
Rack ATS, 10 A/230 V, 12 A/208 V, C14 IN, (12) C13 OUT	AP7721
Rack ATS, 20 A/208 V, 16 A/230 V, C20 IN, (8) C13 (1) C19 OUT	AP7723
Power Modules for N+1 Redundancy	
Symmetra LX 4 kVA Power Module, 220 V/230 V/240 V	SYPM4KI
Parts and Accessories	
Symmetra LX frame electronics module – 230 V	SYAFSU13I
Symmetra LX Input/Output wiring tray – 230 V	SYAFSU14I
Symmetra LX Communications Card	SYAFSU15
Symmetra LX 13 U replacement door	SYAFSU2
Symmetra LX 19 U replacement door	SYAFSU3
Symmetra LX 32 U replacement door	SYAFSU5
Symmetra LX Castor kit – left front, right rear	SYAFSU6
Symmetra LX Castor kit – right front, left rear	SYAFSU7
Symmetra LX top panel	SYAFSU8
Symmetra LX 13 U left side panel	SYAFSU9L
Symmetra LX 19 U left side panel	SYAFSU10L
Symmetra LX 32 U left side panel	SYAFSU12L
Symmetra LX 13 U right side panel	SYAFSU9R
Symmetra LX 19 U right side panel	SYAFSU10R
Symmetra LX 32U right side panel	SYAFSU12R
Power Cords and Adapters	
Power Cord Kit (6 each), Locking, C13 to C14 (90 Degree), 0.6 m	AP8702R
Power Cord Kit (6 each), Locking, C13 to C14, 0.6 m	AP8702S
Power Cord Kit (6 each), Locking, C13 to C14 (90 Degree), 1.2 m	AP8704R
Power Cord Kit (6 each), Locking, C13 to C14, 1.2 m	AP8704S
Power Cord Kit (6 each), Locking, C13 to C14 (90 Degree), 1.8 m	AP8706R