

PT-D210BK *P-touch*

Easy, Compact Label Maker



TOP FEATURES:

SMART, COMPACT DESIGN

- Large, easy-type keyboard and convenient top loading tape design.

EASY-VIEW DISPLAY

- Large, graphical display lets you view text and layout before printing.

CREATE LABELS WITH LESS KEYSTROKES

- Intuitive one-touch keys support quick, easy label formatting.

MULTI-LINE PRINTING

- Create detailed labels with up to 2 lines of text and graphics.

TIME SAVING FEATURES

- Built-in templates and 30 file memory help save time with reprinting.

DURABLE, LAMINATED LABELS

- Create labels for indoor or outdoor use.

HASSLE-FREE APPLICATION

- Split back tapes for easy peel and stick.

SUPPORTS 20 LANGUAGES

- Select the language of your choice.

TAPES FOR MOSTLY ANY APPLICATION

- Standard, extra-strength adhesive, acid free[^], cable and wire, tamper evident, fabric iron-on, super narrow or decorative.

WARRANTY & SUPPORT

- 1-year limited warranty and free support for the life of your product.

PT-D210BK *P-touch*

HARDWARE FEATURES

Display Size	15 characters x 1 line
Maximum Tape Width	12mm
Built-in Memory	Up to 30 labels
Keyboard	QWERTY
Tape Cutter	Manual
Maximum Print Speed	20mm/sec.
Maximum Print Resolution	180 dpi
Maximum Print Height	9.0mm
Power Source	6 x AAA Batteries (optional) AC Power Adapter (optional)
Auto Power Off	Yes

SOFTWARE FEATURES

Number of Fonts	14
Types of Fonts	Helsinki, Brussels, Belgium, Florida, Los Angeles, San Diego, US, Calgary, Atlanta, Adams, Brunei, Istanbul, Sofia, Germany
Number of Font Styles	10
Font Styles	Normal, Bold, Outline, Shadow, Italic, Italic Bold, Italic Outline, Italic Shadow, Vertical, Solid
Font Sizes	Small, Medium, Large
Maximum Print Lines	2
Built-in Symbols	617
Built-in Frames	97
Auto Numbering	1-9
Repeat Printing	Up to 9 copies
Vertical Printing	Yes
Mirror Printing	Yes
Built-in Label Templates	Template Library (17 text templates, 10 pattern templates)
Languages Supported	English, German, French, Spanish, Portuguese, Portuguese-Bra, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovene, Slovak, Croatian, Turkish

ACCESSORIES

AC Power Adapter (optional)	AD-24
-----------------------------	-------

CARTON CONTENTS

PT-D210BK Label Maker
Black on White Standard Laminated TZe Starter Tape 0.47" (12mm) x 13.1' (4m)
User's Guide

SETUP INFORMATION

UPC Code	012502642732
Unit Dimensions	157mm x 150mm x 68mm
Unit Weight	0.5kg
Carton Dimensions	237mm x 98mm x 259mm
Carton Weight	0.86kg

BROTHER STANDARD LAMINATED TZE TAPES*



8 m long / 26.2' long (Unless otherwise indicated)	3.5 mm	6 mm	9 mm	12 mm
Black on White		TZe-211	TZe-221	TZe-231
Black on Clear		TZe-111	TZe-121	TZe-131
Black on Yellow				TZe-631
Black on Blue				TZe-531
White on Black		TZe-315	TZe-325	TZe-335
White on Lime Green ^Δ				TZe-MQG35
White on Berry Pink ^Δ				TZe-MQP35
Red on White			TZe-222	TZe-232
Blue on White			TZe-223	TZe-233
Gold on Black				TZe-334
Black on Red				TZe-431
Black on Green				TZe-731
White on Clear				TZe-135
Red on Clear				TZe-132
Blue on Clear				TZe-133
White on Red				TZe-435

BROTHER EXTRA STRENGTH ADHESIVE LAMINATED TZE-S TAPES*

Black on White	TZe-S211	TZe-S221	TZe-S231
Black on Clear			TZe-S131
Black on Yellow			TZe-S631

BROTHER FLEXIBLE IDENTIFICATION LAMINATED TZE-FX TAPE*

Black on White	TZe-FX231
----------------	-----------

BROTHER SUPER NARROW NON-LAMINATED TZE-N TAPE*

Black on White	TZe-N201
----------------	----------

BROTHER FABRIC IRON-ON TZE-FA TAPE*

Blue on White ^Δ	TZe-FA3
----------------------------	---------

BROTHER ACID-FREE LAMINATED TZE-AF TAPE*

Black on Clear [□]	TZe-AF131
-----------------------------	-----------

To see our full selection of tapes, please visit brother.ca

□ 5 meters long

Δ 3 meters long

* Additional purchase required.



^Δ Claims that adhesive is "acid free" and/or "photo safe" are based upon: 1. Satisfactory test results obtained from Photographic Activity Tests per ISO 14523 and non-acidic pH Tests per TAPPI 509; 2. Certifications from material manufacturers; and 3. Atomic scans of adhesive following removal of backing paper. Brother and its logo are trademarks of Brother Industries Ltd., Japan. All specifications are subject to change without notice. All registered trademarks referenced herein are the property of their respective companies. © 2015 Brother International Corporation (Canada) Ltd.

10/2015 - 42865