



CompuLink fiber optic patch cord

LC (ceramic) to LC (ceramic) 2-fiber aqua jacketed 50/125 OM3 riser rated zipcord.

- * Built using Corning connectors and cordage.
- * Individually bagged.

ANIXTER PART No.	VENDOR PART No.	LENGTH FT.	LENGTH MT.
432270	LCCLCC50+D1	3.3 FT.	1 MT.
432271	LCCLCC50+D2	6.6 FT.	2 MT.
432272	LCCLCC50+D3	10.0 FT.	3 MT.
432273	LCCLCC50+D4	13.1 FT.	4 MT.
432274	LCCLCC50+D5	16.4 FT.	5 MT.
452462	LCCLCC50+D6	19.7 FT.	6 MT.
452469	LCCLCC50+D7	23.0 FT.	7 MT.
452475	LCCLCC50+D8	26.2 FT.	8 MT.
432275	LCCLCC50+D10	32.8 FT.	10 MT.
452477	LCCLCC50+D12	39.4 FT.	12 MT.
432276	LCCLCC50+D15	49.2 FT.	15 MT.
452478	LCCLCC50+D18	59.1 FT.	18 MT.
452498	LCCLCC50+D20	65.6 FT.	20 MT.

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

REV	DESCRIPTION	DATE	BY

DRAWN: G.KRUG	DATE 2/29/12
CHECKED: DATE	
APPROVALS	DATE
ENGINEERING: DATE	
QUALITY: DATE	



CADD REF. No.:
LCLCOM3RISER
DRAWING NO.
LC-LC-OM3-RISER