

Uniprise U/UTP modular panels

Ordering information

Material ID	Product number	Description
760115386	MOD-V-24P	MOD-V Patch Panel , 24 port
760115394	MOD-V-48P	MOD-V Patch Panel, 48 port
760115360	MOD-ANG-24P	MOD Angled Patch Panel, 24 port
760115378	MOD-ANG-48P	MOD Angled Patch Panel, 48 port
760105429	M4800-1U-GS	M4800 1U 48 Port Panel
760109744	M4800A-1U-GS	M4800A 1U Angled 48 Port Panel
760049932	M2000-24 1U	M2000 24-port 1U panel
760049940	M2000-48 2U	M2000 48-port 2U panel
760049957	M2000-24 1U (angled)	M2000A 24-port 1U panel (angled)
760049965	M2000-48 2U (angled)	M2000A 48-port 2U panel (angled)
760065391	M3000-24	M3000 1U 24-Port Panel
760065417	M3000 8-port bezel kit	M3000 Bezel kit
760101220	M2100-24	M2100-1U Modular Patch panel
760077842	M2100-48	M2100-2U Modular Patch Panel
760118182	CS-MOD-1U-36P-Flat	U/UTP Flat Modular Panel, 36 port
760118208	CS-MOD-1U-36P-ANG	U/UTP Angled Modular Panel, 36 port
760118190	CS-MOD-2U-72P-Flat	U/UTP Flat Modular Panel, 72 port
760118216	CS-MOD-2U-72P-ANG	U/UTP Angled Modular Panel, 72 port



M2000

Uniprise ULTRA 10 F/UTP cable

- Electrical performance guaranteed to meet or exceed the channel specifications of ISO/IEC 1 1801 Class E_A and ANSI/TIA-568-C Category 6A
- Supports high-bandwidth applications, including network line speeds of 10 Gbps or greater

Ordering information

Material ID	Product number	Description
8450704/10	10GNS4 GRAY REEL	Category 6A F/UTP Cable, non-plenum, gray jacket, 4 pair count, 1000 ft (305 m) length reel
8450904/10	10GNS4 BLUE REEL	Category 6A F/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel
8451004/10	10GNS4 RED REEL	Category 6A F/UTP Cable, non-plenum, red jacket, 4 pair count, 1000 ft (305 m) length reel
8455704/10	10GNS4 WHITE REEL	Category 6A F/UTP Cable, non-plenum, white jacket, 4 pair count, 1000 ft (305 m) length reel
8463104/10	10GNS4ZH-i BLUE REEL	Category 6A F/UTP Cable, low smoke zero halogen, blue jacket, 4 pair count, 1000 ft (305 m) length, reel
8765304/10	10GS4 WHITE ULTRA 10 REEL	Category 6A F/UTP Cable, plenum, white jacket, 4 pair count, 1000 ft (305 m) length reel
8766404/10	10GS4 GRAY ULTRA 10 REEL	Category 6A F/UTP Cable, plenum, gray jacket, 4 pair count, 1000 ft (305 m) length reel
8765504/10	10GS4 BLUE ULTRA 10 REEL	Category 6A F/UTP Cable, plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel
8767604/10	10GS4 RED ULTRA 10 REEL	Category 6A F/UTP Cable, plenum, red jacket, 4 pair count, 1000 ft (305 m) length reel



10GNS4