


VideoEdge / victor Network Architecture



Ordering Information

Model Numbers	Description
VideoEdge Micro NVR	
ADVEM02N0NP4	VideoEdge Micro NVR with 4 IP camera license and 2 TB storage, 4 PoE ports built-in, no RAID; supports up to 8 IP cameras
ADVEM02N0NP8	VideoEdge Micro NVR with 4 IP camera license and 2 TB storage, 8 PoE ports built-in, no RAID; supports up to 8 IP cameras
VideoEdge Desktop NVR	
ADVED00N0N4B	VideoEdge Desktop NVR with 4 IP camera licenses, 0 TB storage, 2 NIC
ADVED02N0N4B	VideoEdge Desktop NVR with 4 IP camera licenses, 2 TB JBOD, 2 NIC
ADVED04N0N4B	VideoEdge Desktop NVR with 4 IP camera licenses, 4 TB JBOD, 2 NIC
ADVED06N0N4B	VideoEdge Desktop NVR with 4 IP camera licenses, 6 TB JBOD, 2 NIC
VideoEdge 2U NVR	
ADVER00R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 0 TB storage, 4 NIC, includes RAID controller and redundant power supply
ADVER06N0N2B	VideoEdge 2U NVR, 4 IP camera licenses, 6 TB RAID 0, 4 NIC, includes RAID controller and redundant power supply
ADVER08R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 8 TB RAID 0, 4 NIC, includes RAID controller and redundant power supply
ADVER12N0N2B	VideoEdge 2U NVR, 4 IP camera licenses, 12 TB RAID 0, 4 NIC, includes RAID controller and redundant power supply
ADVER12R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 12 TB RAID 5 (16 total), 4 NIC, redundant power supply
ADVER18R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 18 TB RAID 5 (24 total), 4 NIC, redundant power supply
ADVER20R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 20 TB RAID 5 (24 total), 4 NIC, redundant power supply
ADVER30R5N2B	VideoEdge 2U NVR, 4 IP camera licenses, 30 TB RAID 5 (36 total), 4 NIC, redundant power supply
VideoEdge Rack Mount NVR Server	
ADVER06N0DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 6 TB RAID 0, 4 NIC, redundant power supply
ADVER18R5DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 18 TB RAID 5 (24 total), 4 NIC, redundant power supply
ADVER36R5DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 36 TB RAID 5 (42 total), 4 NIC, redundant power supply
ADVER48R5DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 48 TB RAID 5 (54 total), 4 NIC, redundant power supply
ADVER66R5DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 66 TB RAID 5 (72 total), 4 NIC, redundant power supply
ADVER90R5DF	VideoEdge Rack Mount NVR, 4 IP camera licenses, 90 TB RAID 5 (96 total), 4 NIC, redundant power supply
VideoEdge NVR HD Kits	
ADVER03TBTAD	Compatible with VideoEdge 2U NVR, 3 TB Hot Plug HD Kit w/Tray
ADVER04TBTAD	Compatible with VideoEdge 2U NVR, 4 TB Hot Plug HD Kit w/Tray
ADVER06TBTAD	Compatible with VideoEdge 2U NVR, 6 TB Hot Plug HD Kit w/Tray
ADVE730HD06TBI	Compatible with VideoEdge Rack Mount NVR Server, 6 TB Internal HD Kit
ADVE730HD06TBT	Compatible with VideoEdge Rack Mount NVR Server, 6 TB Hot Plug HD Kit
VideoEdge NVR Accessories	
ADVEMRACKITA	VideoEdge Micro NVR rackmount ear kit
ADVEMWALKITA	VideoEdge Micro NVR wall mount bracket kit
ADVEDRACKKIT1	VideoEdge Desktop NVR, Rack Mount Server Kit Brackets
ADVER04GBH2A	VideoEdge 4 GB Memory Kit for ADVERxxxx2A recorders
ADVEFHBA730	VideoEdge Rack Mount NVR Server, Fiber HBA Adapter Kit