


Mounting Accessories

Surface Mount Boxes



SBX-ACE

Surface Mount Box for AX-DM, GT-D, IF-DA, IX-BA, IX-DA, JF-D, JF-DA, JK-DA, JO-DA, JP-DA, KB-DAR, or KB-DAR-M and one Access Control Device



SBX-DVF

Surface Mount Box for JF-DVF, JK-DVF, JO-DVF, or JP-DVF



SBX-AXDVF

Surface Mount Box for AX-DVF



SBX-DVF-P

Surface Mount Box for AX-DVF-P, JF-DVF-HID, JK-DVF-AC, or JK-DVF-HID



SBX-ISDVF

Surface Mount Box for IS-DVF, IS-IPDVF, IS-SS, IX-DF, IX-DF-HID, IX-DF-RP10, or IX-SS



SBX-ISDVF-P

Surface Mount Box for IS-DVF-HID, IS-DVF-RP10, IS-IPDVF-HID, or IS-IPDVF-RP10



SBX-ISDVFRA

Surface Mount Box for IS-DVF-2RA, IS-DVF-2RA-FR, IS-SS-2RA, IS-SS-2RA-R, IS-SS-RA, IS-SS-RA-R, IX-DF-2RA, IX-DF-2RA-FR, IX-SS-2RA, IX-SS-RA, IX-SS-RA-FR, JP-DVF-HID, or JP-DVF-RP10



SBX-1G

Surface Mount Box for LE-SS-1G



SBX-2G

Surface Mount Box for IS-SS-2G, IS-SSR-2G, IE-JA, IE-SS/A, IE-SSR, LE-DA, LE-SS/A, LE-SSR, or NI-JA



SBX-NVP

Surface Mount Box for LS-NVP/C

Features (SBX-ACE)

- Vandal resistant
- Hood provides weather resistance
- Includes blank stainless steel cover for wide range of mounting options
- Openings at bottom allow for moisture drainage

Features (SBX-DVF, SBX-AXDVF, SBX-DVF-P, SBX-ISDVF, SBX-ISDVF-P, SBX-ISDVFRA)

- Hood provides weather resistance
- Includes space inside for wiring
- Mounts directly to wall
- Openings at bottom allow for moisture drainage

Features (SBX-1G)

- Weather resistant
- Includes space inside for wiring
- Mounts directly to wall surface

Features (SBX-2G)

- Weather resistant
- Includes space inside for wiring
- Mounts to 1-gang box or ring
- Can mount directly to wall surface
- Includes hardware for mounting intercom

Features (SBX-NVP)

- Weather resistant
- Includes space inside for wiring
- Mounts to 1-gang box or ring
- Can mount directly to wall surface
- Powder-coated white baked epoxy finish

Specifications

Material SBX-ACE, SBX-DVF-P, SBX-ISDVF, SBX-ISDVF-P, SBX-ISDVFRA, SBX-1G, SBX-2G: 18GA stainless steel

SBX-DVF, SBX-AXDVF: 16GA stainless steel (outer layer), 18GA stainless steel (inner layer)

SBX-NVP: 1/8" rolled steel

Mounting SBX-ACE, SBX-DVF, SBX-AXDVF, SBX-DVF-P, SBX-ISDVF, SBX-ISDVF-P, SBX-ISDVFRA: surface mount directly to wall, 1-gang box, or 2-gang box with included hardware (8 x 32 with T-15 Torx head)

SBX-1G, SBX-2G, SBX-NVP: surface mount directly to wall or 1-gang box with included hardware (8 x 32 with T-15 Torx head)

SBX-ACE

