

Analog Page Controls



Analog 2000 Series™			VPU
A	1 Zone ◆◆▲ • Basic Zone or Area of Paging One-Way V-2000A +12 2.60"H x 7.70"W x 5.30"D (6.60cm x 19.56cm x 13.46cm) 2.6lbs (1.2kg)		
B	1 Zone Enhanced ◆◆▲ • Phantom Zone™ Allows Paging to All Speakers But Limits Music to Selected Speakers One-Way V-2001A +20 One-Way European Version* V-2001A-E +20 7.10"H x 9.00"W x 2.40"D (18.03cm x 22.86cm x 6.10cm) 3.7lbs (1.68kg) *International Version - Power Requirements: 230 Vac/5A		
C	3 Zones ◆◆▲ • Three Zones of One-Way Paging Plus All Call One-Way V-2003A +20 7.10"H x 10.00"W x 3.00"D (18.03cm x 25.40cm x 7.62cm) 4.1lbs (1.86kg) One-Way European Version* V-2003A-E +20 7.10"H x 10.00"W x 3.00"D (18.16cm x 25.40cm x 7.62cm) 4.1lbs (1.86kg) Talkback V-2003AHF +10 7.10"H x 10.00"W x 3.00"D (18.03cm x 25.40cm x 7.62cm) 5.6lbs (2.54kg) Talkback European Version* V-2003AHF-E +10 7.10"H x 10.00"W x 3.00"D (18.16cm x 25.40cm x 7.62cm) 5.6lbs (2.54kg) *International Version - Power Requirements: 230 Vac/5A		
D	6 Zones ◆◆▲ • Six Zones of One-Way Paging, All Call, 3 Programmable Zone Groups One-Way V-2006A +30 10.90"H x 13.00"W x 2.70"D (27.69cm x 33.20cm x 6.86cm) 6.2lbs (2.81kg) One-Way European Version* V-2006A-E +30 10.90"H x 13.00"W x 2.70"D (27.69cm x 33.20cm x 6.86cm) 6.2lbs (2.81kg) Talkback V-2006AHF +20 10.90"H x 13.00"W x 2.70"D (27.69cm x 33.20cm x 6.86cm) 7.5lbs (3.40kg) Talkback European Version* V-2006AHF-E +20 10.90"H x 13.00"W x 2.70"D (27.69cm x 33.20cm x 6.86cm) 7.5lbs (3.40kg) *International Version - Power Requirements: 230 Vac/1.0A		

Analog Page Controls			VPU
PBX Loop Start Trunk, Electronic Key Line, Single Line Phone			
E	1 Zone ◆ Talkback V-9941A -6 8.25"H x 4.65"W x 2.30"D (20.96cm x 11.81cm x 5.84cm) 1.5lbs (0.68kg)		
Station Level/FXS Adapters			
1 Zone ●			
F	For use with One-Way Controllers V-9970 -4 8.25"H x 4.50"W x 2.35"D (20.96cm x 11.43cm x 5.97cm) 1.5lbs (0.68kg)		
G	For use with One-Way or Talkback Controllers V-9940 -4 8.20"H x 4.55"W x 2.30"D (20.83cm x 11.56cm x 5.84cm) 1.7lbs (0.77kg)		
H	PagePal Interface ◆◆▲● V-5335700 0 2.50"H x 6.00"W x 4.00"D (6.35cm x 15.24cm x 10.16cm) 2.0lbs (0.91kg)		

What is a Zone?

A zone can be any area, any size that you determine. It's usually an area where the same overhead pages would need to be heard.

Within a zone you can have as many different types of speakers as you want. From basic overhead round ceiling speakers, to high-fidelity sound, to horns for water-proof areas, to door entry speakers and many more.



Step 1 Select a Page Control

Easy Selection Considerations:

- Number of Zones
- One-Way Broadcast Only or Talkback (Includes One-Way) Two-Way HandsFree
- Special Features

Features Telephone Access

Model #	One-Way Page Controls				Talkback Page Controls		
	V-2000A	V-2001A	V-2003A	V-2006A	V-2003AHF	V-2006AHF	
Number of Zones	1	1	3	6	3	6	
Background Music	•	•	•	•	•	•	
All Call	•	•	•	•	•	•	
Group Call				•		•	
Emergency Page Override		•	•	•	•	•	
Night Ring/Time Clock Tones		•	•	•	•	•	
Valcom Power Units Provided	+ 12	+ 20	+ 20	+ 30	+ 10	+ 20	
Telephone Access	FXO FXD Port	PBX Loop Start Trunk Port	◆	•	•	•	•
		Electronic Key Line Position	■	•	•	•	•
		Dedicated Single Line Phone Set	▲	•	•	•	•
Telephone Access	FXS Port	PBX Ground Start Trunk Port	■	•	•	•	
		Page Port (Telephone System Dependant)	▲	•	•	•	•
		Centrex or C.O. Line PBX Analog Station Port (Loop Disconnect Required)		●	Use V-9970	Use V-9970	Add V-9940

Look for these orange symbols when selecting page controls