



SPECIFICATION SHEET

09-K300LP



KUT-GARD® KEVLAR® GLOVE WITH COWHIDE LEATHER PALM - MEDIUM WEIGHT

- Kevlar® fiber shell provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity
- Cowhide leather palm provides comfort, durability, excellent abrasion resistance, and breathability
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing

APPLICATIONS

- Material handling
- Glass handling
- Fishing industries
- Sanitation
- General maintenance
- Woodworking
- Waste handling
- Recycling

CARE INSTRUCTIONS

Dry clean only.

TECHNICAL DATA

MATERIAL	Cowhide leather / Kevlar®			
CONSTRUCTION	Shell: Kevlar® stitch / Palm: 100% cowhide leather			
COLOR	Shell: Yellow / Palm: Grey			
CUFF STYLE	Knitwrist			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE SIZE	S	M	L	XL
	18.5" x 15.0" x 7.9" 47cm x 38cm x 20cm		19.7" x 15.0" x 7.9" 50cm x 38cm x 23cm	
CASE WEIGHT	S	M	L	XL
	22.0 lbs 10.0 kg	25.4 lbs 11.5 kg	27.6 lbs 12.5 kg	29.8 lbs 13.5 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 4443	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16) ASTM F1790-05 ANSI Cut Level 4					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	-
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-




BARCODES

ITEM	BAG	DOZEN	CASE
09-K300LP/S	---	01616314003554	02616314003554
09-K300LP/M	---	01616314003561	02616314003561
09-K300LP/L	---	01616314003578	02616314003578
09-K300LP/XL	---	01616314003585	02616314003585

DIMENSIONS (in/cm)

	S	M	L	XL
A	8.9 / 22.5	9.6 / 24.5	10.0 / 25.5	10.6 / 27.0
B	3.7 / 9.5	3.9 / 10.0	4.3 / 11.0	4.5 / 11.5
H	White	Red	Yellow	Green



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.