

# **CUBE-iT PLUS Accessories**

#### Fan Kit

Attaches over the vents in the side of the CUBE-IT PLUS Cabinet. Draws air into the cabinet, pressurizing the cabinet and forcing warm air out of the side vents. Fan Filter Kit reduces dust and can be mounted internally for security or externally for convenience; filter kit and filters sold separately. Includes mounting hardware and cable ties. Available in 115 VAC, 50/60 Hz, 37 dB Fan with 5'L (1.5 m) attached power cord and NEMA 5-15 plug; and 230 VAC, 50/60 Hz, 37 dB Fan with 5'L (1.5 m) attached power cord and NEMA 6-15P plug.

#### Light

Light attaches to the bottom, top or side of cabinet and provides 8 Watts of fluorescent light with on/off switch. 115 VAC with 6' (1.8 m) attached power cord and NEMA 5-15P plug. 1U rack-mount version also available.

#### **Termination Block Panel**

Attaches to rear panel of CUBE-iT PLUS Cabinet. Supports six 110D-style 100pair blocks or four 66-style blocks/H89D brackets. Clear finish.

### Vertical Cable Manager

Vertical Cable Managers can be used in 60"H (1520 mm) and 72"H (1830 mm) cabinets only. Openings align with rack-mount units, 2.7"W x 5"D (69 mm x 130 mm) usable interior space. Adjusts front-to-rear within cabinet; fingers manage patch cords. Must be installed before rack-mount equipment.

## Horizontal Wire Management Bar

Attaches to the rear of the equipment mounting rail to secure premise cables after termination on patch panels. Includes mounting hardware and 12 cable ties.

Part Number	Description	Shipping Weight Ib (kg)
12804-701	Fan Kit, 100 CFM, 115 VAC, 50/60 Hz, NEMA 5-15P	4 (1.8)
12804-702	Fan Kit, 100 CFM, 230 VAC, 50/60 Hz, NEMA 6-15P	4 (1.8)
12805-X01	Filter Kit for Fan	4 (1.8)
12806-001	Filters for Fan, Box of 6	1 (0.5)
12803-701	Light	3 (1.4)
13287-501	Termination Block Panel 11.5 x 19 (292 x 480 mm), 66 Block	4 (1.8)
13288-501	Termination Block Panel 11.5 x 19 (292 x 480 mm), 110 Block	4 (1.8)
13485-760	Cable Manager for 60 (1520) Cabinet	9 (4.1)
13485-772	Cable Manager for 72 (1830) Cabinet	10 (4.5)
11837-X01	Horizontal Wire Management Bar	2 (0.9)
k=color: 2=Compu	ter Beige, 7=Black	÷