

IP Megapixel PTZ Cameras

1.3 and 2.0MPx IP PTZ Cameras



OVERVIEW

The TruVision® IP Megapixel PTZ represents the next generation of H.264-based PTZ video surveillance technology. Fully programmable and designed to deliver unmatched performance, the TruVision IP Megapixel PTZ produces high-quality IP video in a variety of challenging environments. The progressive-scan 1.3 and 2.0MPx 20X optical zoom camera offers clear images at short- and long-range distances, while the digital wide dynamic range functionality enables viewing in bright and dark areas simultaneously.

The TruVision IP Megapixel PTZ allows you to capture what is important when using some of the new features, such as intelligent tracking and region of interest. While allowing you to mask off areas that require privacy.

Three housing options are available: indoor/outdoor pendant, indoor flush and indoor surface. The indoor/outdoor pendant is IP66-rated for outdoor use and includes a heater and fan, and is also wall mount ready (GEA-102) and can be pendant-mounted using an available threaded adapter. The indoor flush and surface models offer a fast, simple installation right out of the box.

STANDARD FEATURES

- 1/3-inch progressive scan CMOS
- H.264/MPEG/MJPEG compression technology
- Resolution up to 30 FPS
- Privacy Masks, Intelligent tracking, Region of Interest (ROI)
- Built-in micro SD card slot provided, supports up to 32GB
- POE+ or 24VAC
- Built-in Web page for PC-based control
- ONVIF/PSIA open standards compliant
- Indoor and outdoor mounts available
- Pendant models compatible with CyberDome/Legend GEA Series wall mounts

IP Megapixel PTZ Cameras

1.3 and 2.0MPx IP PTZ Cameras

North America
T 855-286-8889

Latin America
T 561-998-6114

Ordering Information

NTSC

TVP-3101	TruVision® 1.3MPx, NTSC, Pan/Tilt/Zoom Dome Pendant Outdoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-3102	TruVision 1.3MPx, NTSC, Pan/Tilt/Zoom Dome Surface Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-3103	TruVision 1.3MPx, NTSC, Pan/Tilt/Zoom Dome Flush Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-3104	TruVision 2MPx, NTSC, Pan/Tilt/Zoom Dome Pendant Outdoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-3105	TruVision 2MPx, NTSC, Pan/Tilt/Zoom Dome Surface Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-3106	TruVision 2MPx, NTSC, Pan/Tilt/Zoom Dome Flush Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC

PAL

TVP-1101	TruVision 1.3MPx, PAL, Pan/Tilt/Zoom Dome Pendant Outdoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-1102	TruVision 1.3MPx, PAL, Pan/Tilt/Zoom Dome Surface Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-1103	TruVision 1.3MPx, PAL, Pan/Tilt/Zoom Dome Flush Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-1104	TruVision 2MPx, PAL, Pan/Tilt/Zoom Dome Pendant Outdoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-1105	TruVision 2MPx, PAL, Pan/Tilt/Zoom Dome Surface Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC
TVP-1106	TruVision 2MPx, PAL, Pan/Tilt/Zoom Dome Flush Mount Indoor, CMOS, True D/N, DWDR, Motorized IR Cut Filter, H.264, ONVIF/PSIA, 20X Optical Zoom, SD Card Slot, PoE+/24VAC

Accessories

1060050A	Pendant Adapter for PTZ, 1 1/4 NPT, Rubber Boot, UTC Gray (Used with Outdoor Pendant)
GEA-102	Wall Mount, Cast Aluminum
GEA-104	Parapet Swing-Arm Mount
GEA-105	Corner-Mount Adapter
GEA-106	Pole-Mount Adapter
GEA-107	Roof-Mount Adapter

IP/PTZ part number schema

TV	P	-	1	1	XX
Device Type B=Bullet C=Camera D=Dome P=PTZ W=Wedge T=Turret			Format 1=IP PAL 2=Analog PAL 3=IP NTSC 4=Analog NTSC		Sequence/ Camera Specifics Series 1=First



interlogix.com

Specifications subject to change without notice.

© 2013 United Technologies Corporation.

All rights reserved.

Interlogix is part of UTC Building & Industrial Systems,
a unit of United Technologies Corporation.

310-3736 2013/12 (76475)